


UNITRONIC® SENSOR M8-M8

M8 M8

/ , M8 M8, PUR , 3/4 , / , LED, A , IP65 / IP67 / IP68,

www.lappgroup.com/assemblyfinder 가



Lapp



Space-saving due to compact dimensions.

가

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR M8-M8

가 가

UV-

PWIS PVC

DIN VDE 0472
UL : E249137
: UL 1581 FT-2

: 0.25 mm²

: 3-pin: bn (1), bu (3), bk (4) 4-pin: bn (1), wh (2), bu (3), bk (4)
: PUR,

ETIM 5:	ETIM 5.0 Class-ID: EC001855
	ETIM 5.0 Class: -
ETIM 6:	ETIM 6.0 Class-ID: EC001855
	ETIM 6.0 Class :
:	: CuSn : Ni/Au ,
	: TPU, ,
:	: 5 x
	: 10 x
가:	IP65/IP67/IP68
():	/
	-25°C +90°C (PUR/PVC)
	-40°C - +80°C
	-25°C - +80°C
:	A-Standard
(A):	4 A

, 가 가 . (.) 가 .

가 VAT 가 가 .
UL-Zertifizierungen sind dem Datenblatt zu entnehmen

UNITRONIC® SENSOR M8-M8

		/	(m)	Design	LED	(V)	PU
22260206	AB-C3-M8MS-0,3PU R-M8FS	3	0.3	-	no	60	1
22260207	AB-C3-M8MS-0,6PU R-M8FS	3	0.6	-	no	60	1
22260208	AB-C3-M8MS-1,0PU R-M8FS	3	1	-	no	60	1
22260209	AB-C3-M8MS-2,0PU R-M8FS	3	2	-	no	60	1
22260938	AB-C3-M8MS-5,0PU R-M8FS	3	5	-	no	60	1
22260210	AB-C3-M8MS-0,3PU R-M8FA	3	0.3	-	no	60	1
22260211	AB-C3-M8MS-0,6PU R-M8FA	3	0.6	-	no	60	1
22260212	AB-C3-M8MS-1,0PU R-M8FA	3	1	-	no	60	1
22260213	AB-C3-M8MS-2,0PU R-M8FA	3	2	-	no	60	1
22260214	AB-C3-M8MS-0,3PU R-M8FA-2L	3	0.3	-	2 LEDs	24	1
22260215	AB-C3-M8MS-0,6PU R-M8FA-2L	3	0.6	-	2 LEDs	24	1
22260216	AB-C3-M8MS-1,0PU R-M8FA-2L	3	1	-	2 LEDs	24	1
22260379	AB-C3-M8MS-1,5PU R-M8FA-2L	3	1.5	-	2 LEDs	24	1
22260217	AB-C3-M8MS-2,0PU R-M8FA-2L	3	2	-	2 LEDs	24	1
4-							
22260313	AB-C4-M8MS-0,3PU R-M8FS	4	0.3	-	no	30	1
22260314	AB-C4-M8MS-0,6PU R-M8FS	4	0.6	-	no	30	1
22260315	AB-C4-M8MS-1,0PU R-M8FS	4	1	-	no	30	1
22260316	AB-C4-M8MS-2,0PU R-M8FS	4	2	-	no	30	1
22260923	AB-C4-M8MS-5,0PU R-M8FS	4	5	-	no	30	1

(23.12.2023)

UNITRONIC® SENSOR M8-M8

		/	(m)	Design	LED	(V)	PU
22260922	AB-C4-M8MS-10,0P UR-M8FS	4	10	-	no	30	1
22260059	AB-C4-M8MS-0,3PU R-M8FA	4	0.3	-	no	30	1
22260060	AB-C4-M8MS-0,6PU R-M8FA	4	0.6	-	no	30	1
22260061	AB-C4-M8MS-1,0PU R-M8FA	4	1	-	no	30	1
22260062	AB-C4-M8MS-2,0PU R-M8FA	4	2	-	no	30	1