


Verteilerbox M12

M12 / 가 /M23 가

M12



Lapp



M23

M12 quick-locking system, optional diagnostic LEDs (PNP)

LABS frei

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Verteilerbox M12

E- : E75770

: PVC
: PUR,

ETIM 5:

ETIM 5.0 Class-ID: EC002585
ETIM 5.0 Class-Description: Passive sensor-actuator interface

ETIM 6:

ETIM 6.0 Class-ID: EC002585

ETIM 6.0 Class : /

가:

IP65/IP67 (M23)

IP65/IP67/IP69

():

-25°C bis +75°C (M23)-30°C bis +90°C
-40 ° C ~ + 90 ° C, () -5 ° C bis

+80 °

2 A

4 A

가 VAT 가 가 .

() .

(M8: 22260606, M12: 22260605)

UL-Zertifizierungen sind dem Datenblatt zu entnehmen

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Verteilerbox M12

		(m)	/	
22260010	AB-B4-M12-4-5,0PUR	5	4	no
22260011	AB-B4-M12-4-10,0PUR	10	4	no
22260014	AB-B8-M12-8-5,0PUR	5	8	no
22260015	AB-B8-M12-8-10,0PUR	10	8	no
22260018	AB-B4-M12L-4-5,0PUR	5	4	LEDs
22260019	AB-B4-M12L-4-10,0PUR	10	4	LEDs
22260970	AB-B6-M12L-6-5,0PUR	5	6	LEDs
22260022	AB-B8-M12L-8-5,0PUR	5	8	LEDs
22260023	AB-B8-M12L-8-10,0PUR	10	8	LEDs
가				
22260005	AB-B4-M12-4-C	-	4	no
22260007	AB-B8-M12-8-C	-	8	no
22260001	AB-B4-M12L-4-C	-	4	LEDs
22260003	AB-B8-M12L-8-C	-	8	LEDs
M23				
22260618	AB-B6-6-L-M23	-	6	LEDs
22260012	AB-B4-M12-8-5,0PUR	5	4	no
22260013	AB-B4-M12-8-10,0PUR	10	4	no
22260016	AB-B8-M12-16-5,0PUR	5	8	no
22260017	AB-B8-M12-16-10,0PUR	10	8	no
22260020	AB-B4-M12L-8-5,0PUR	5	4	LEDs
22260021	AB-B4-M12L-8-10,0PUR	10	4	LEDs
22260024	AB-B8-M12L-16-5,0PUR	5	8	LEDs
22260025	AB-B8-M12L-16-10,0PUR	10	8	LEDs
가				
22260006	AB-B4-M12-8-C	-	4	no
22260008	AB-B8-M12-16-C	-	8	no
22260002	AB-B4-M12L-8-C	-	4	LEDs
22260004	AB-B8-M12L-16-C	-	8	LEDs

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16