

UNITRONIC® SENSOR M12-M12

M12 M12

/ , 3, 4, 5, 8 , M12 / M12 M12 / , A-codiert, PUR , IP65 / IP67 / IP68,

www.lappgroup.com/assemblyfinder 가



Lapp



Space-saving due to compact dimensions.

(가)

가

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12-M12

UV-

PWIS PVC

DIN VDE 0472
UL : E249137
: UL 1581 FT-2

: 0,34 mm²(8- : 0,25 mm²)

: 3 : bn (1), bu (3), bk (4) 4 : bn (1), wh (2), bu (3), bk (4) 5 : (1), bn (2), gn (3), ye4), gy (1), wh (2), bu (3), bk
5), pk (6), bu (7), rd (8)
: PUR,

ETIM 5:

ETIM 5.0 Class-ID: EC001855

ETIM 5.0 Class: -

ETIM 6:

ETIM 6.0 Class-ID: EC001855

ETIM 6.0 Class :

: : CuSn : Ni/Au ,
: TPU, ,
: 5 x
: 10 x

가:

IP65/IP67

():

Plug/socket -25°C to +90°C

-40°C - +80°C

-25°C - +80°C

:

A-Standard

(A):

4 A

2 A (8-pin)

, 가 가 . (.) 가 .

가 VAT 가 가 .

UL-Zertifizierungen sind dem Datenblatt zu entnehmen

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12-M12

		(m)	Design	LED	(V)	PU
22260233	AB-C3-M12MS-0,3PUR-M12FS	0.3	-	no	250	1
22260234	AB-C3-M12MS-0,6PUR-M12FS	0.6	-	no	250	1
22260235	AB-C3-M12MS-1,0PUR-M12FS	1	-	no	250	1
22260236	AB-C3-M12MS-2,0PUR-M12FS	2	-	no	250	1
22260237	AB-C3-M12MS-0,3PUR-M12FA	0.3	-	no	250	1
22260238	AB-C3-M12MS-0,6PUR-M12FA	0.6	-	no	250	1
22260239	AB-C3-M12MS-1,0PUR-M12FA	1	-	no	250	1
22260240	AB-C3-M12MS-2,0PUR-M12FA	2	-	no	250	1
22260261	AB-C3-M12MS-0,3PUR-M12FA-2L	0.3	-	2 LEDs	24	1
22260262	AB-C3-M12MS-0,6PUR-M12FA-2L	0.6	-	2 LEDs	24	1
22260263	AB-C3-M12MS-1,0PUR-M12FA-2L	1	-	2 LEDs	24	1
22260264	AB-C3-M12MS-2,0PUR-M12FA-2L	2	-	2 LEDs	24	1
4-						
22260328	AB-C4-M12MS- 0,3PUR-M12FS	0.3	-	no	250	1
22260329	AB-C4-M12MS- 0,6PUR-M12FS	0.6	-	no	250	1
22260330	AB-C4-M12MS- 1,0PUR-M12FS	1	-	no	250	1
22260331	AB-C4-M12MS- 2,0PUR-M12FS	2	-	no	250	1
22260702	AB-C4-M12MS-5,0PUR-M12FS	5	-	no	250	1
22260332	AB-C4-M12MS- 0,3PUR-M12FA	0.3	-	no	250	1
22260333	AB-C4-M12MS- 0,6PUR-M12FA	0.6	-	no	250	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12-M12

		(m)	Design	LED	(V)	PU
22260334	AB-C4-M12MS-1,0PUR-M12FA	1	-	no	250	1
22260335	AB-C4-M12MS-2,0PUR-M12FA	2	-	no	250	1
22260851	AB-C4-M12MS-10,0PUR-M12FA	10	-	no	60	1
22260336	AB-C4-M12MS-0,3PUR-M12FA-3L	0.3	-	3 LEDs	24	1
22260337	AB-C4-M12MS-0,6PUR-M12FA-3L	0.6	-	3 LEDs	24	1
22260338	AB-C4-M12MS-1,0PUR-M12FA-3L	1	-	3 LEDs	24	1
22260339	AB-C4-M12MS-2,0PUR-M12FA-3L	2	-	3 LEDs	24	1
22262195	AB-C4-M12MS-5,0PUR-M12FA-3L	5	-	3 LEDs	24	1
22262199	AB-C4-M12MS-10,0PUR-M12FA-3L	10	-	3 LEDs	24	1
22260304	AB-C4-M12MA-0,3PUR-M12FS	0.3	gewinkelt-gerade	no	250	1
22260305	AB-C4-M12MA-0,6PUR-M12FS	0.6	gewinkelt-gerade	no	250	1
22260306	AB-C4-M12MA-1,0PUR-M12FS	1	gewinkelt-gerade	no	250	1
22260307	AB-C4-M12MA-2,0PUR-M12FS	2	gewinkelt-gerade	no	250	1
5-						
22260410	AB-C5-M12MS-0,3PUR-M12FS	0.3	-	no	60	1
22260411	AB-C5-M12MS-0,6PUR-M12FS	0.6	-	no	60	1
22260412	AB-C5-M12MS-1,0PUR-M12FS	1	-	no	60	1
22260413	AB-C5-M12MS-2,0PUR-M12FS	2	-	no	60	1
22260063	AB-C5-M12MS-0,3PUR-M12FA	0.3	-	no	60	1
22260064	AB-C5-M12MS-0,6PUR-M12FA	0.6	-	no	60	1
22260065	AB-C5-M12MS-1,0PUR-M12FA	1	-	no	60	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR M12-M12

		(m)	Design	LED	(V)	PU
22260066	AB-C5-M12MS-2,0PUR-M12FA	2	-	no	60	1
22260067	AB-C5-M12MS-0,3PUR-M12FA-3L	0.3	-	3 LEDs	24	1
22260068	AB-C5-M12MS-0,6PUR-M12FA-3L	0.6	-	3 LEDs	24	1
22260069	AB-C5-M12MS-1,0PUR-M12FA-3L	1	-	3 LEDs	24	1
22260070	AB-C5-M12MS-2,0PUR-M12FA-3L	2	-	3 LEDs	24	1
8-polig						
22260097	AB-C8-M12MS-0,3PUR-M12FS	0.3	-	no	30	1
22260098	AB-C8-M12MS- 0,6PUR-M12FS	0.6	-	no	30	1
22260099	AB-C8-M12MS-1,0PUR-M12FS	1	-	no	30	1
22260042	AB-C8-M12MS- 2,0PUR-M12FS	2	-	no	30	1
22260137	AB-C8-M12MS-0,3PUR-M12FA	0.3	-	no	30	1
22260138	AB-C8-M12MS-0,6PUR-M12FA	0.6	-	no	30	1
22260139	AB-C8-M12MS1,0PUR-M12FA	1	-	no	30	1
22260140	AB-C8-M12MS-2,0PUR-M12FA	2	-	no	30	1