

EPIC® Contacts for circular connectors

M23, LS1 EPIC® , 가

Made in Germany



ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

가 VAT 가 가 .

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® Contacts for circular connectors

		Version		/ PU	
74033001	POWER LS1 A SCM 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	LSI A1, A3, G	10
74033000	POWER LS1 A SCM 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	LSI A1, A3, G	100
74034001	POWER LS1 F SCM 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	LS1 F6, F7	10
74034000	POWER LS1 F SCM 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	LS1 F6, F7	100
74033101	POWER LS1 A SCM 2mm AU 0.5-2.5	2 mm	0.5 - 2.5 mm ²	LSI A1, A3, G	10
74033100	POWER LS1 A SCM 2mm AU 0.5-2.5	2 mm	0.5 - 2.5 mm ²	LSI A1, A3, G	100
74034101	POWER LS1 F SCM 2mm AU 0.5-2.5	2 mm	0.5 - 2.5 mm ²	LS1 F6, F7	10
74034100	POWER LS1 F SCM 2mm AU 0.5-2.5	2 mm	0.5 - 2.5 mm ²	LS1 F6, F7	100
44420103	POWER LS1 F SCM 2mm AU 4.0	2 mm	4.0 mm ²	LS1 F6, F7	100
72400001	SIGNAL M23 SCM 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	M23 (D-Sub)	10
72400000	SIGNAL M23 SCM 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	M23 (D-Sub)	100
72402001	SIGNAL M23 SLM 1mm AU 1.0	1 mm		M23 (D-Sub)	10
72402000	SIGNAL M23 SLM 1mm AU 1.0	1 mm		M23 (D-Sub)	100
72401000	M23 SCM 2mm AU 1.0-2.5	2 mm		M23 (D-Sub)	100
72403100	SIGNAL M23 SLM 2mm AU 1.0-2.5	2 mm		M23 (D-Sub)	10
72403000	SIGNAL M23 SLM 2mm AU 1.0-2.5	2 mm		M23 (D-Sub)	100
74020601	M23/LS1 BCMS 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	M23 (D-Sub), LS1 D6, LS1 A6	10
74200600	M23/LS1 BCMS 1mm AU 0.14-1.0	1 mm	0.14 - 1.0 mm ²	M23 (D-Sub), LS1 D6, LS1 A6	100
72402601	SIGNAL M23 BLMS 1mm AU 1.0	1 mm		M23 (D-Sub)	10
72402600	SIGNAL M23 BLMS 1mm AU 1.0	1 mm		M23 (D-Sub)	100
72401601	SIGNAL M23 BCMS 2mm AU 1,0-2,5	2 mm female	1.0 - 2.5 mm ²	M23 (D-Sub)	10
72401600	-	2 mm female	1.0 - 2.5 mm ²	M23 (D-Sub)	100

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

EPIC® Contacts for circular connectors

		Version		/ PU
72404100	SIGNAL M23 BLMS 2mm AU 2.5	2 mm	M23 (D-Sub)	10
72404000	SIGNAL M23 BLMS 2mm AU 2.5	2 mm	M23 (D-Sub)	100
74034501	M23/LS1 BCMD 1mm AU 0.14-1.0	1 mm mm ²	0.14 - 1.0 M23 (D-Sub), LS1 D6, LS1 A6	10
74034500	M23/LS1 BCMD 1mm AU 0.14-1.0	1 mm mm ²	0.14 - 1.0 M23 (D-Sub), LS1 D6, LS1 A6	100
44420104	POWER LS1 D BCMD 2mm AU 4.0	2 mm	4 mm ² D6, A6	10
44420105	POWER LS1 D BCMD 2mm AU 4.0	2 mm	4 mm ² D6, A6	100
44429001	POWER LS1 BCBG 2mm 1.0-2.5 (3000) RE	2 mm female	1.0 - 2.5 mm ² LS1 D6, A6	1
44429370	POWER LS1 D BCMF 2mm AU 0.5-2.5	2 mm	0,5-2,5mm ² LS1 D6, A6	100
2mm contacts, female, crimp				
44429371	POWER LS1 D BCMF 2mm AU 0.5-2.5	2 mm	0,5-2,5mm ² LS1 D6, A6	10

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® Contacts for circular connectors



(25.04.2024)

EPIC® Contacts for circular connectors



(25.04.2024)