

# EPIC® POWER LS1.5

EPIC® POWER LS1.5                      1.5

Made in Germany

가



ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

가    VAT            가    가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

EPIC® POWER LS1.5

		Version		/ PU
44429335	LS1.5 A SCEM 3,6MM AU 1,0-2,5	3.6 mm male 1.0 - 2.5 mm <sup>2</sup>	A1, A3	10
44429337	LS1.5 A SCEM 3,6MM AU 4,0-6,0	3.6 mm male 4.0 - 6.0 mm <sup>2</sup>	A1, A3	10
44429338	LS1.5 A SCEM 3,6MM AU 6,0-10,0	3.6 mm male 6.0 - 10.0 mm <sup>2</sup>	A1, A3	10
44429326	LS1.5 F SCEM 3,6MM AU 1,0-2,5	3.6 mm male 1.0 - 2.5 mm <sup>2</sup>	F6	10
44429327	LS1.5 F SCEM 3,6MM AU 2,5-4,0	3.6 mm male 2.5 - 4.0 mm <sup>2</sup>	F6	10
44429328	LS1.5 F SCEM 3,6MM AU 4,0-6,0	3.6 mm male 4.0 - 6.0 mm <sup>2</sup>	F6	10
44429329	LS1.5 F SCEM 3,6MM AU 6,0-10,0	3.6 mm male 6.0 - 10.0 mm <sup>2</sup>	F6	10
44429340	LS1.5 A SCEM 2MM AU 0,25-1,0	2 mm male 0.25 - 1.0 mm <sup>2</sup>	A1, A3	10
44429341	LS1.5 A SCEM 2MM AU 0,75-1,5	2 mm male 0.75 - 1.5 mm <sup>2</sup>	A1, A3	10
44429330	LS1.5 F SCEM 2MM AU 0,25-1,0	2 mm male 0.25 - 1.0 mm <sup>2</sup>	F6	10
44429331	LS1.5 F SCEM 2MM AU 0,75-1,5	2 mm male 0.75 - 1.5 mm <sup>2</sup>	F6	10
44429332	LS1.5 F SCEM 2MM AU 1,0-2,5	2 mm male 1.0 - 2.5 mm <sup>2</sup>	F6	10
44429333	LS1.5 F SCEM 2MM AU 2,5-4,0	2 mm male 2.5-4.0 mm <sup>2</sup>	F6	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## EPIC® POWER LS1.5



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16