

EPIC® H-D 1.6 machined contacts

EPIC®

Machined EPIC H-D contacts are suitable for industrial data and signal transmission. Silver or gold plating guarantee reliable contacting.

High quality contacts for data and signal transmission with 1.6mm
Choice of silver or gold plating



High quality contacts for data and signal transmission with 1.6mm
Choice of silver or gold plating
Connection cross sections from 0.14mm² to 2.5mm² available for combined data and power transmission

With the appropriate tools, good contacting is created quickly and easily

ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

가 VAT 가 가 .

(16.07.2024)



EPIC® H-D 1.6 machined contacts

	Article description	Contact type	(mm ²)			(mm)	Packaging unit
13162000	H-D 1.6		0.14 - 0.37	1	Ag	8.0	100
13163000	H-D 1.6		0.14 - 0.37	1	Ag	8.0	100
13162100	H-D 1.6		0.5	2	Ag	8.0	100
13163100	H-D 1.6		0.5	2	Ag	8.0	100
13162200	H-D 1.6		0.75 - 1	3	Ag	8.0	100
13163200	H-D 1.6		0.75 - 1	3	Ag	8.0	100
13162300	H-D 1.6		1.5	4	Ag	8.0	100
13163300	H-D 1.6		1.5	4	Ag	8.0	100
13162400	H-D 1.6		2.5	5	Ag	5.8	100
13163400	H-D 1.6		2.5	5	Ag	5.8	100
13162500	H-D 1.6		0.14 - 0.37	1	Au	8.0	100
13163500	H-D 1.6		0.14 - 0.37	1	Au	8.0	100
13162600	H-D 1.6		0.5	2	Au	8.0	100
13163600	H-D 1.6		0.5	2	Au	8.0	100
13162700	H-D 1.6		0.75 - 1	3	Au	8.0	100
13163700	H-D 1.6		0.75 - 1	3	Au	8.0	100
13162800	H-D 1.6		1.5	4	Au	8.0	100
13163800	H-D 1.6		1.5	4	Au	8.0	100
13162900	H-D 1.6		2.5	5	Au	5.8	100
13163900	H-D 1.6		2.5	5	Au	5.8	100

(16.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-D 1.6 machined contacts



(16.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16