EPIC® H-A 3 AG

혁신적인 금속 그리고 플라스틱 하우징 디자인

Locks reliably, does not burn, and protects the internal insert from dust and moisture: these are just three of the essential features of our newly revamped rectangular connector housing. The lightweight polyamide panel-mount base is also halogen-free, UV-resistant and securely sealed to the device or machine thanks to the NBR material.

정보

The panel-mount base of the EPIC® H-A 3 series is now available with a new design, with a marking arrow and an integrated seal. The single lever is no longer made of metal, but plastic.





- 기계 및 플랜트 엔지니어링
- 기계적 저항성
- 튼튼함
- 방수

장점

The EPIC® H-A 3 series comprises the smallest housings in the heavy-duty industrial connector range and ensures secure connections in the smallest of spaces.
The panel mount housing is mateable to many commercially available grommet housings.
With open base for cable entry into the housing or control cabinet.
The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.
The locking takes place using a plastic single lever.

응용 범위

To protect the connector insert from environmental influences.
For use with many EPIC® rectangular connector inserts.

최근 업데이트 (28.03.2024)
©2024 Lapp Group - all rights reserved.
제품 관리 http://lappkorea.lappgroup.com
해당하는 data sheet 에서 최근 자료를 찾을 수 있습니다.
PN 0456 / 02_03.16

EPIC® H-A 3 AG

For connecting devices and machines to the power supply.
Suitable for outdoor use.

제품 특성

H-A case: Wall base
1 레버
플랫 가스켓 포함

기술 데이터

분류 ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 class 설명: 산업용 커넥터 하우징
분류 ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
재료:	하우징: 파우더-코트된 아연 다이-케스팅, 회색 레버: 아연-도금 강철 씰링: NBR 하우징: 회색 열가소성 수지, 흑색 레버: 아연-도금 강철 씰링: NBR
보호 평가:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-시험됨:	인증된 생산 제어: VDE-REG. 번호: B437 UL-테스트 완료: UL 파일 번호: E75770
온도 범위:	-40°C to +100°C, short-term up to +125°C

비고

사진은 각각의 제품 상세 이미지를 대변하지는 않습니다.
가격은 VAT 및 할증료가 없는 가격. 비즈니스 고객에게만 판매

©2024 Lapp Group - all rights reserved.

EPIC® H-A 3 AG

품번	Article description	M	재료	색상	피스 / PU
H-A 하우징 : 패널-장착 기반 (직선)					
10422500	H-A 3 MAG	AG	아연 다이-캐스팅	회색	10
10422000	H-A 3 AG gr	AG	서모플라스틱	회색	10
10422200	H-A 3 AG bk	AG	서모플라스틱	흑색	10

최근 업데이트 (28.03.2024)
©2024 Lapp Group - all rights reserved.
제품 관리 http://lappkorea.lappgroup.com
해당하는 data sheet 에서 최근 자료를 찾을 수 있습니다.