

FLEXIMARK® LA Labels

FLEXIMARK® LA (:)

LA 16.9-9 FLEXIMARK® YE (M3251010)



가 , , (, , , ...)

(:)

24

FLEXIMARK® 가

가 가

DIN A4

ETIM 5:

ETIM 5.0 Class-ID: EC001288
ETIM 5.0 class :

(24.04.2024)



FLEXIMARK® LA Labels

ETIM 6:

:
:
:
:

ETIM 6.0 Class-ID: EC001288
ETIM 6.0 Class :

:
: 0.05 mm
-40°C to +150°C
: +10 °C

가 VAT 가 가 .) LCK 32 640 640 1 PU
FLEXIMARK®

FLEXIMARK® LA Labels

		x (mm)		PU	PU
83256199	FLEXIMARK® LA label 7-8 YE	7.0 x 8.0	560	5600	1
83256228	FLEXIMARK® LA label 11-8 YE	11.0 x 8.0	420	4200	1
83256231	FLEXIMARK® LA label 12-6 YE	12.0 x 6.0	611	6110	1
83256204	FLEXIMARK® LA label 15-6 YE	15.0 x 6.0	517	5170	1
83256234	FLEXIMARK® LA label 16-8 YE	16.0 x 8.0	315	3150	1
83256207	FLEXIMARK® LA label 16.9-7 YE	16.9 x 7.0	400	4000	1
83256210	FLEXIMARK® LA label 16.9-9 YE	16.9 x 9.0	310	3100	1
83256213	FLEXIMARK® LA label 20-8 YE	20.0 x 8.0	280	2800	1
83256216	FLEXIMARK® LA label 25-12 YE	25.0 x 12.0	161	1610	1
83256219	FLEXIMARK® LA label 25.6-10 YE	25.6 x 10.0	196	1960	1
83256240	FLEXIMARK® LA label 30.5-12.7 YE	30.5 x 12.7	110	1100	1
83256222	FLEXIMARK® LA label 46.9-9 YE	46.9 x 9.0	124	1240	1
83256225	FLEXIMARK® LA label 56-21.8 YE	56.0 x 21.8	39	390	1
83256243	FLEXIMARK® LA label 60-30 YE	60.0 x 30.0	27	270	1
83256237	FLEXIMARK® LA label 80-7.5 YE	80.0 x 7.5	74	740	1
83256198	FLEXIMARK® LA label 7-8 WH	7.0 x 8.0	560	5600	1
83256227	FLEXIMARK® Etikett LA 11-8 WH	11.0 x 8.0	420	4200	1
83256230	FLEXIMARK® LA label 12-6 WH	12.0 x 6.0	611	6110	1
83256203	FLEXIMARK® LA label 15-6 WH	15.0 x 6.0	517	5170	1
83256233	FLEXIMARK® LA label 16-8 WH	16.0 x 8.0	315	3150	1
83256206	FLEXIMARK® LA label	16.9 x 7.0	400	4000	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



FLEXIMARK® LA Labels

		x (mm)		PU	PU
	16.9-7 WH				
83256209	FLEXIMARK® LA label 16.9-9 WH	16.9 x 9.0	310	3100	1
83256212	FLEXIMARK® LA label 20-8 WH	20.0 x 8.0	280	2800	1
83256215	FLEXIMARK® LA label 25-12 WH	25.0 x 12.0	161	1610	1
83256218	FLEXIMARK® LA label 25.6-10 WH	25.6 x 10.0	196	1960	1
83256239	FLEXIMARK® LA label 30.5-12.7 WH	30.5 x 12.7	110	1100	1
83256221	FLEXIMARK® LA label 46.9-9 WH	46.9 x 9.0	124	1240	1
83256224	FLEXIMARK® LA label 56-21.8 WH	56.0 x 21.8	39	390	1
83256242	FLEXIMARK® LA label 60-30 WH	60.0 x 30.0	27	270	1
83256236	FLEXIMARK® LA label 80-7.5 WH	80.0 x 7.5	74	740	1
83256200	FLEXIMARK® LA label 7-8 SR	7.0 x 8.0	560	5600	1
83256229	FLEXIMARK® LA label 11-8 SR	11.0 x 8.0	385	3850	1
83256232	FLEXIMARK® LA label 12-6 SR	12.0 x 6.0	611	6110	1
83256235	FLEXIMARK® LA label 16-8 SR	16.0 x 8.0	315	3150	1
83256241	FLEXIMARK® LA label 30.5-12.7 SR	30.5 x 12.7	110	1100	1
83256244	FLEXIMARK® LA label 60-30 SR	60.0 x 30.0	27	270	1
83256238	FLEXIMARK® LA label 80-7.5 SR	80.0 x 7.5	74	740	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16