

# FLEXIMARK® Flexilabel TFL

FLEXIMARK® Flexilabel TFL are blank label rolls for marking cables with character holders or for installation. Text can be printed on the labels using our marking software with a thermal transfer printer.



PTE, PTEF CAB ( " " )  
Suitable for IP20 - IP40 Environments like public buildings such as schools, offices, hospital and malls

Installation labels

Easy to print via FLEXIMARK®  
software Flexisoft and FLEXIMARK®

thermal transfer printer SQUIX, EOS5 or EOS2

ETIM 5: ETIM 5.0 Class-ID: EC001288  
ETIM 5.0 class :  
ETIM 6: ETIM 6.0 Class-ID: EC001288  
ETIM 6.0 Class :

:

(24.04.2024)



# FLEXIMARK® Flexilabel TFL

Upon request: Yellow, green, blue, red, brown, black

Polypropylene laminate

-20°C to +80°C

가	VAT	가	가 .	.	) LCK 32	640	640	1	PU
FLEXIMARK®									

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



FLEXIMARK® Flexilabel TFL

		x (mm)	PU	PU
83263023	Flexilabel TFL 9,5x17,5 WH	9.5 x 17.5	252	1
83263021	Flexilabel TFL 9,5x28 WH	9.5 x 28.0	500	1
83263019	Flexilabel TFL 9,5x35 WH	9.5 x 35.0	1000	1
83263025	Flexilabel TFL 9,9x66 WH	9.9 x 66.0	1000	1
83263032	Flexilabel TFL 12x48 WH	12.0 x 48.0	252	1
83263024	Flexilabel TFL 9,5x17,5 YE	9.5 x 17.5	252	1
83263022	Flexilabel TFL 9,5x28 YE	9.5 x 28.0	500	1
83263020	Flexilabel TFL 9,5x35 YE	9.5 x 35.0	1000	1
83263026	Flexilabel TFL 9,9x66 YE	9.9 x 66.0	1000	1
83263028	Flexilabel TFL 9,9x66 GN	9.9 x 66.0	252	1
83263029	Flexilabel TFL 9,9x66 BN	9.9 x 66.0	252	1
83263030	Flexilabel TFL 9,9x66 RD	9.9 x 66.0	252	1
83263031	Flexilabel TFL 9,9x66 BK	9.9 x 66.0	252	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16