

H05V2-K EMOSS

Harmonised assembly flex in large cardboard box

<HAR> 가 (:<VDE><HAR>)
 . <HAR> 가 .

90°C



<HAR> 가 (:<VDE><HAR>)
 . <HAR> 가 .

Ideally suited to meet the stricter thermal requirements of the new IEC-EN-(NBN NEN) 61439 standard

: IEC 60332-1-2

EN 50525-2-31

5(IEC 60228)
 : PVC, 90°C, TI3

가 가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

(23.04.2024)

H05V2-K EMBOSS

:	ETIM 5.0 Class	:	
:	VDE 0295	5/ IEC 60228	5
:	가	가	
:	4x Außendurchmesser		
:	U0/U: 300/500 V		
:	2000 V		
:	-10°C ~ +90°C		
:		: 5°C	

www.lappkabel.de/en/cable-standradlengths () 가 .

가 VAT 가 가 .

H05V2-K EMBOSS

		(mm ²)	(mm)	m/	(kg/km)	(kg/km)
4515001K	/	0.5	2.5	3000	4.8	9
4515002K	/	0.75	2.7	2500	7.2	11
4515003K	/	1	2.8	2000	9.6	14
4515011K		0.5	2.5	3000	4.8	9
4515012K		0.75	2.7	2500	7.2	11
4515013K		1	2.8	2000	9.6	14
4515021K		0.5	2.5	3000	4.8	9
4515022K		0.75	2.7	2500	7.2	11
4515023K		1.0	2.8	2000	9.6	14
4515031K		0.5	2.5	3000	4.8	9
4515032K		0.75	2.7	2500	7.2	11
4515033K		1.0	2.8	2000	9.6	14
4515041K		0.5	2.5	3000	4.8	9
4515042K		0.75	2.7	2500	7.2	11
4515043K		1.0	2.8	2000	9.6	14
4515051K		0.5	2.5	3000	4.8	9
4515052K		0.75	2.7	2500	7.2	11
4515053K		1.0	2.8	2000	9.6	14
4515061K		0.5	2.5	3000	4.8	9
4515062K		0.75	2.7	2500	7.2	11
4515063K		1.0	2.8	2000	9.6	14
4515071K		0.5	2.5	3000	4.8	9
4515072K		0.75	2.7	2500	7.2	11
4515073K		1	2.8	2000	9.6	14
4515081K		0.5	2.5	3000	4.8	9
4515082K		0.75	2.7	2500	7.2	11
4515083K		1.0	2.8	2000	9.6	14
4515091K		0.5	2.5	3000	4.8	9
4515092K		0.75	2.7	2500	7.2	11
4515093K		1.0	2.8	2000	9.6	14
4515111K		0.5	2.5	3000	4.8	9
4515112K		0.75	2.7	2500	7.2	11
4515113K		1.0	2.8	2000	9.6	14
4515121K		0.5	2.5	3000	4.8	9

(23.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet
 PN 0456 / 02_03.16



H05V2-K EMBOSS

		(mm ²)	(mm)	m/	(kg/km)	(kg/km)
4515122K		0.75	2.7	2500	7.2	11
4515123K		1.0	2.8	2000	9.6	14
4515141K		0.5	2.5	3000	4.8	9
4515142K		0.75	2.7	2500	7.2	11
4515143K		1	2.8	2000	9.6	14

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16