

Cable trolley system for round and flat cables

Lapp Group

(Knowledge center-cable accessories)



()

Not suitable for applications in explosive environments

Round- and flat cables are not allowed to be combined side by side or below each other

3

"b"가 가 ().

C- 6 m

()

ETIM 5: ETIM 5.0 Class-ID: EC002935
ETIM 5.0 class :

ETIM 6: ETIM 6.0 Class-ID: EC002935
ETIM 6.0 Class :

: : 20 Kg

(24.04.2024)



Cable trolley system for round and flat cables

: : : 6
: -40°C ~ +120°C

CIBES® INOMEK AB

가 VAT 가 가 .

(24.04.2024)

Cable trolley system for round and flat cables

		System	Max. flat cable dimensions mm	max. round cable diameter mm	/ PU
62200421		C30	15.0 x 54.0	-	1
62200442	30x54	C30	30.0 x 54.0	-	1
62200477	22x54 b	C30	22.0 x 54.0	-	1
62200420		C30	30.0 x 54.0	-	1
62200482	22x54 b	C30	22.0 x 54.0	-	1
62200422		C30	30.0 x 54.0	-	1
62200483	22x54 b	C30	22.0 x 54.0	-	1
62200464	22x52	C40	22.0 x 52.0	-	1
62200479	22x72	C40	22.0 x 72.0	-	1
62200419	22x97	C40	22.0 x 97.0	-	1
62200480	22x132	C40	22.0 x 132.0	-	1
62200446	35x72	C40	35.0 x 72.0	-	1
62200457	35x97	C40	35.0 x 97.0	-	1
62204505	35x132	C40	35.0 x 132.0	-	1
62200465	22x52	C40	22.0 x 52.0	-	1
62200488	22x72	C40	22.0 x 72.0	-	1
62200418	22x97	C40	22.0 x 97.0	-	1
62200489	22x132	C40	22.0 x 132.0	-	1
62200447	35x72	C40	35.0 x 72.0	-	1
62200458	35x97	C40	35.0 x 97.0	-	-

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

Cable trolley system for round and flat cables

		System	Max. flat cable dimensions mm	max. round cable diameter mm	/ PU
62200466	35x132 , , C40	C40	35.0 x 132.0	-	1
62200484	22x52 , , C40	C40	22.0 x 52.0	-	1
62200485	22x72 , , C40	C40	22.0 x 72.0	-	1
62200417	22x97 , , C40	C40	22.0 x 97.0	-	1
62200486	22x132 , , C40	C40	22.0 x 132.0	-	1
62200448	35x72 , , C40	C40	35.0 x 72.0	-	1
62200459	35x97 , , C40	C40	35.0 x 97.0	-	1
62204504	35x132 , , C40	C40	35.0 x 132.0	-	1
62200434		C30	-	-	1
62200435		C30	-	-	1
62200478		C40	-	-	1
62200481		C40	-	-	1
62200437		-	-	10.0 - 16.0	1
62200438	17-25 mm	-	-	17.0 - 25.0	1
62200439	mm , , 26-36	-	-	26.0 - 36.0	1
62200436		C30, C40	-	-	1
62200440	C- , 6 m	C30	-	-	1
62200424		C30	-	-	1
62200427	가	C30	-	-	1
62200429		C30	-	-	1
62200425		C30	-	-	1
62200432	Arm, 800 mm	C30	-	-	1
62200444	C , 6m, C40	C40	-	-	1
62200445	, C40	C40	-	-	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

Cable trolley system for round and flat cables

		System	Max. flat cable dimensions mm	max. round cable diameter mm	/ PU
62200456	, C40	C40	-	-	1
62200461	, C40	C40	-	-	1
62200449	, C40	C40	-	-	1
62200467	, 800mm, C40	C40	-	-	1
62200460	11-725	C30, C40	-	-	1
62200430	, 400 mm	C30, C40	-	-	1
62200431	, 630 mm	C30, C40	-	-	1
62200433		C30, C40	-	-	1
62200471	-	-	-	-	1
62200428		-	-	-	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16