

PROTECT Box

가



Green-yellow shrink tube: For identifying and marking earthing connectors and cables

()

UV ()

UL 224 (:)
UL : E476215(:)

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

PROTECT Box

ETIM 5:

ETIM 5.0 Class-ID: EC000217

ETIM 5.0 Class-Description: Schrumpfschlauch

ETIM 6:

ETIM 6.0 Class-ID: EC000217

ETIM 6.0 Class :

:

가

:

: 20 kV/mm

:

: 2:1

:

-

:

, ,

:

-55°C +135°C

: +90°C

가 VAT 가 가 .

PROTECT BOX

	Article description	(mm)	, +- 0.1 mm	PU (m)	PU
61742423	PROTECT Box 1,2/0,6 BK	1.2 - 0.6	0.41	12	1
61742424	PROTECT Box 1,6/0,8 BK	1.6 - 0.8	0.43	12	1
61742425	PROTECT Box 2,4/1,2 BK	2.4 - 1.2	0.51	12	1
61742426	PROTECT Box 3,2/1,6 BK	3.2 - 1.6	0.51	12	1
61742427	PROTECT Box 4,8/2,4 BK	4.8 - 2.4	0.51	10	1
61742428	PROTECT Box 6,4/3,2 BK	6.4 - 3.2	0.64	8	1
61742429	PROTECT Box 9,5/4,7 BK	9.5 - 4.7	0.64	7	1
61742430	PROTECT Box 12,7/6,4 BK	12.7 - 6.4	0.64	6	1
61742431	PROTECT Box 19,1/9,5 BK	19.1 - 9.5	0.77	5	1
61742433	PROTECT Box 25,4/12,7 BK	25.4 - 12.7	0.89	3	1
61742434	PROTECT Box 1,2/0,6 TR	1.2 - 0.6	0.41	12	1
61742435	PROTECT Box 1,6/0,8 TR	1.6 - 0.8	0.43	12	1
61742436	PROTECT Box 2,4/1,2 TR	2.4 - 1.2	0.51	12	1
61742437	PROTECT Box 3,2/1,6 TR	3.2 - 1.6	0.51	12	1
61742438	PROTECT Box 4,8/2,4 TR	4.8 - 2.4	0.51	10	1
61742439	PROTECT Box 6,4/3,2 TR	6.4 - 3.2	0.64	8	1
61742440	PROTECT Box 9,5/4,7 TR	9.5 - 4.7	0.64	7	1
61742441	PROTECT Box 12,7/6,4 TR	12.7 - 6.4	0.64	6	1
61742442	PROTECT Box 19,1/9,5 TR	19.1 - 9.5	0.77	5	1
61742443	PROTECT Box 25,4/12,7 TR	25.4 - 12.7	0.89	3	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16