

Shrink tube PROTECT Set



가

()

UV ()

UL 224 (:)
 UL : E476215(:)

PROTECT
 Content:
 50x 50 mm Shrink tube PROTECT 1,6/0,8 BK
 50x 50 mm Shrink tube PROTECT 1,6/0,8 TR

(25.04.2024)

Shrink tube PROTECT Set

- 50 x 50 mm Shrink tube PROTECT 2,4/1,2 BK
- 50 x 50 mm Shrink tube PROTECT 2,4/1,2 TR
- 20 x 50 mm Shrink tube PROTECT 3,2/1,6 BK
- 20 x 50 mm Shrink tube PROTECT 3,2/1,6 TR
- 20 x 50 mm Shrink tube PROTECT 3,2/1,6 YE
- 20 x 50 mm Shrink tube PROTECT 3,2/1,6 WH
- 10 x 50 mm Shrink tube PROTECT 4,8/2,4 BK
- 10 x 50 mm Shrink tube PROTECT 4,8/2,4 TR
- 10 x 50 mm Shrink tube PROTECT 4,8/2,4 YE
- 10 x 50 mm Shrink tube PROTECT 4,8/2,4 BU
- 15 x 50 mm Shrink tube PROTECT 6,4/3,2 BK
- 15 x 50 mm Shrink tube PROTECT 6,4/3,2 WH
- 15 x 50 mm Shrink tube PROTECT 6,4/3,2 YE
- 15 x 50 mm Shrink tube PROTECT 6,4/3,2 BU
- 15 x 50 mm Shrink tube PROTECT 9,5/4,7 BK
- 15 x 50 mm Shrink tube PROTECT 9,5/4,7 BU
- 20 x 50 mm Shrink tube PROTECT 12,7/6,4 BK
- 20 x 50 mm Shrink tube PROTECT 12,7/6,4 RD
- 5 x 100 mm Shrink tube PROTECT 19,1/9,5 BK
- 5 x 100 mm Shrink tube PROTECT 19,1/9,5 BU
- 5 x 180 mm Shrink tube PROTECT 25,4/12,7 BK
- 1 x HOT GUN

ETIM 5:

ETIM 5.0 Class-ID: EC000217
 ETIM 5.0 Class-Description: Schrumpfschlauch

ETIM 6:

ETIM 6.0 Class-ID: EC000217
 ETIM 6.0 Class :

:

: 20 kV/mm

:

: 2:1

:

:

-55°C +135°C
 : +90°C

가 VAT 가 가 .

(25.04.2024)



Shrink tube PROTECT Set

	Article description
61742465	PROTECT Set

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16