


# TRONIC

Mobile and flexible solutions to unwind, store and transport single core coils and spools.

TRONIC products are optimized for LAPP single core coils H05V-K and H07V-K (Maxi ring) as well as for LAPP single core spools.



Easy and mobile handling and storage of single core Coils and spools and increases occupational safety and tidy workplaces  
 Direct bundling of single cores at the operation site leads to efficient assembly  
 User-friendly solution because of short setup times due to an easy refill  
 No twisting / kinking through horizontal pull  
 Mounting of barcodes enables to use kanban solutions , furthermore FLEXIMARK® markings are also possible

Transporting, storing and unwinding of single core coils and spools  
 Overcoming stairs and other barriers with the Climber version  
 All in one compact mobile storage and unwinding solution for the operational site

TRONIC module consists of 2 TRONIC boxes mounted on a holder  
 TRONIC Single core-cart S12:  
 Capacity for 12 to 18 single core spools (depending on spools width)  
 Cart with tool holder  
 TRONIC Module single core cart Climber with stair climber and optionally a tray for tools (article no.: 85001640)

:

Fits for cable rings:  
 Cable outer diameter: max. 10 mm  
 Coil Diameter: max. 295 mm  
 Inner diameter: 80-180 mm  
 Height: max. 80 mm

:

TRONIC : 7 kg  
 Max. loading TRONIC Single core-cart S12:  
 1. Level: 60 kg  
 2. Level: 40 kg  
 3. Level: 30 kg

(24.04.2024)



# TRONIC

:

Painted steel

TRONIC Meccanica Nicoletti S.R.L (社)

가 VAT 가 가 .

(24.04.2024)

				(mm)	(kg)
85001632	TRONIC Box	-	1	D=310.0, H=103.0	0.7
85001624	TRONIC	12	12 TRONIC	L=670.0, W=610.0, H=950.0	19
85001629	TRONIC	48	48 TRONIC	L=865.0, W=770.0, H=1460.0	106
85001625	TRONIC		2 TRONIC	L=335.0, W=335.0, H=280.0	2.6
85001621	TRONIC 6x2	-	6 TRONIC Module	L=610.0, W=600.0, H=1270.0	29
85001622	TRONIC 18x2	-	18 TRONIC Module	L=840.0, W=820.0, H=1400.0	93
85001639	TRONIC Module single core cart Climber	-	6 TRONIC Module	L=710.0, W=680.0, H=1360.0	40
85001628	TRONIC Single core-cart S12	-		L=620.0, W=590.0, H=1160.0	20
85001637	TRONIC cover		1 transparentn í v í ko	-	-

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

TRONIC

