

SKINDICHT® BL-M hex.

SKINDICHT® BL-M, brass blind plugs hexagonal for closing pre-threaded holes, assembling with spanner



Withstands temperatures up to +100 °C.

Mounted O-ring enables liquid-tight sealing of the threaded/through hole and a higher degree of protection (up to IP 68).

Simple assembly by using an open-end wrench.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

For closing an unoccupied metric threaded hole on the housing.

Withstands high chemical and mechanical stress.

DIN EN 60423

DIN IEC 62444

Dummy plug made of stainless steel on request

(14.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® BL-M hex.

ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class :

:

Fitted with FKM O-ring (-20°C to +200°C)

:

:

가:

O- : NBR

:

IP 68 - 5 bar

-20°C +100°C

가 VAT 가 가 .

(14.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® BL-M hex.

	Article designation / size	SW (mm)	, C mm	Thread length D mm	Ø (mm)	/ PU
SKINDICHT® BL-M hex.						
52103405	M 12 x 1,5	16	8.0	5	17.8	50
52103415	M 16 x 1,5	20	8.0	5	22.0	50
52103425	M 20 x 1,5	24	9.5	6	26.4	50
52103435	M 25 x 1,5	29	11.0	7	31.9	50
52103445	M 32 x 1,5	36	12.0	8	39.6	25
52103455	M 40 x 1,5	45	13.0	8	49.5	25
52103465	M 50 x 1,5	54	15.0	9	59.0	10
52103475	M 63 x 1,5	67	16.0	10	73.5	10
52103405LF	M 12 x 1,5	16	8.0	5	17.8	50
52103415LF	M 16 x 1,5	20	8.0	5	22.0	50
52103425LF	M 20 x 1,5	24	9.5	6	26.4	50
52103435LF	M 25 x 1,5	29	11.0	7	31.9	50
52103445LF	M32x1,5	36	12.0	8	39.6	25
52103455LF	M40x1,5	45	13.0	8	49.5	25
52103465LF	M50x1,5	54	15.0	9	59.0	10
52103475LF	M63x1,5	67	16.0	10	73.5	10

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

(14.05.2024)