

SKINDICHT® ME-M ATEX

SKINDICHT® ME-M ATEX, ,

가



O- 가

가

II / 2G+1D

DIN EN 60079-0
DIN EN 60079-7
DIN EN 60079-31

DIN EN 60423
DIN IEC 62444

(24.04.2024)



SKINDICHT® ME-M ATEX

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

CE 0637 Ex II 2G

Ex eb IIC

Ex II 1D Ex ta IIIC

IECEx IBE 13.0028X

:

:

O- : NBR

:

-30°C +90°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® ME-M ATEX

	(thread) , M1	(thread) , M2	(mm)	SW (mm)	(mm)	Ø (mm)	/ PU
SKINDICHT® ME-M ATEX							
52104580	12 x 1.5	16 x 1.5	17	18	5	20.0	50
52104581	16 x 1.5	20 x 1.5	20	22	6	24.0	50
52104582	20 x 1.5	25 x 1.5	22.5	27	6.5	30.0	50
52104583	25 x 1.5	32 x 1.5	21.5	34	6.5	37.7	25
52104584	32 x 1.5	40 x 1.5	23	42	7	46.0	25
52104585	40 x 1.5	50 x 1.5	26	54	8	59.0	25
52104586	50 x 1.5	63 x 1.5	32	67	9	73.0	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16