

SKINDICHT® MA-M/PG

SKINDICHT® MA-M/PG, PG 가



Allows the easy transition from a metric male thread to a PG female thread.

Withstands temperatures up to +200 °C.

Available for thread sizes up to PG42 or up to M63.

Mold A in easy-grip knurled design for easy screwing in of the adapter even in oily environments; mold B in smooth design.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

For applications with different types of threads.

Withstands high chemical and mechanical stress.

Suitable for outdoor use.

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

O-

:

-60°C +200°C

:

(12.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® MA-M/PG

가 VAT 가 가 .

(12.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® MA-M/PG

	(thread), M1	(thread), PG	/ PU
SKINDICHT® MA-M / PG			
52104200	16 x 1.5	7	100
52104200LF	16 x 1.5	7	100
52104210	20 x 1.5	9	50
52104210LF	20 x 1.5	9	50
52104220	25 x 1.5	11	50
52104230	25 x 1.5	13.5	50
52104240	25 x 1.5	16	50
52104250	32 x 1.5	16	25
52104260	32 x 1.5	21	25
52104270	40 x 1.5	21	25
52104280	50 x 1.5	29	10
52104290	63 x 1.5	36	10
52104300	63 x 1.5	42	10
52104220LF	25 x 1.5	11	50
52104230LF	25 x 1.5	13.5	50
52104240LF	25 x 1.5	16	50
52104250LF	32 x 1.5	-	25
52104260LF	32 x 1.5	21	25
52104270LF	40 x 1.5	21	25
52104280LF	50 x 1.5	29	10
52104290LF	63 x 1.5	36	10
52104300LF	63 x 1.5	42	10