

SKINTOP® GMP-GL NPT

SKINTOP® GMP-GL NPT

(thread)

SKINDICHT®

NPT

가 (surface)

ETIM 5:

ETIM 5.0 Class-ID: EC000940
ETIM 5.0 :

(RAL 7001)
(RAL 7035)
(RAL 9005)

-20°C +100°C

가 VAT 가 가 .

(19.08.2024)



SKINTOP® GMP-GL NPT

	Article designation / size	(mm)	SW (mm)	/ PU
SKINTOP® GMP-GL NPT				
53019301	NPT 3/8"	5.0	22	100
53019311	NPT 1/2"	6.0	27	100
53019321	NPT 3/4"	7.0	36	100
53019331	NPT 1"	7.0	42	100
SKINTOP® GMP-GL NPT				
53019305	NPT 3/8"	5.0	22	100
53019315	NPT 1/2"	6.0	27	100
53019325	NPT 3/4"	7.0	36	100
53019335	NPT 1"	7.0	42	100
SKINTOP® GMP-GL NPT				
53019300	NPT 3/8"	5.0	22	100
53019310	NPT 1/2"	6.0	27	100
53019320	NPT 3/4"	7.0	36	100
53019330	NPT 1"	7.0	42	100