

SKINDICHT® MA-PG/M

SKINDICHT® MA-PG/M,

, PG

, PG



Allows easy transition from a PG external thread to a metric internal thread.

Withstands temperatures up to +200 °C.

Available for thread sizes till PG36/M40.

Mold A in easy-grip knurled design for easy screwing in of the adapter even in oily environments; mold B in smooth design.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

For applications with different types of threads.

Withstands high chemical and mechanical stress.

Suitable for outdoor use.

PG

m A :

m B :

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

:

-60°C +200°C

가 VAT 가 가 .

(23.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® MA-PG/M

	m	PG	(thread) , M2	/ PU
SKINDICHT® MA-PG/M				
52104490	B	7	12 x 1.5	100
52104491	B	9	16 x 1.5	50
52104492	A	11	16 x 1.5	50
52104493	B	11	20 x 1.5	50
52104494	B	13.5	20 x 1.5	50
52104495	A	16	20 x 1.5	50
52104495LF	A	16	20 x 1.5	50
52104496	B	16	25 x 1.5	50
52104497	A	21	20 x 1.5	50
52104498	A	21	25 x 1.5	50
52104499	B	21	32 x 1.5	50
52104500	A	29	25 x 1.5	25
52104501	A	29	32 x 1.5	25
52104502	B	29	40 x 1.5	10
52104503	A	36	40 x 1.5	10
52104490LF	B	7	12 x 1.5	100
52104491LF	B	9	16 x 1.5	50
52104492LF	A	11	16 x 1.5	50
52104493LF	B	11	20 x 1.5	50
52104494LF	B	13.5	20 x 1.5	50
52104496LF	B	16	25 x 1.5	50
52104497LF	A	21	20 x 1.5	50
52104498LF	A	21	25 x 1.5	50
52104499LF	B	21	32 x 1.5	50
52104500LF	A	29	25 x 1.5	25
52104501LF	A	29	32 x 1.5	25
52104502LF	B	29	40 x 1.5	10
52104503LF	A	36	40 x 1.5	10

(23.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16