

SKINDICHT® BL-M

SKINDICHT® BL-M, -



Withstands temperatures up to +200 °C.

Simple assembly by using a slotted screwdriver.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

For closing an unoccupied metric threaded hole on the housing.
Withstands high chemical and mechanical stress.

UL E79903

(15.05.2024)



SKINDICHT® BL-M

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class :

:

UL File E79903

:

Fitted with FKM O-ring (-20°C to +200°C)

:

:

O- : NBR

가:

IP 54

IP 68 (with O-ring)

:

With O-ring: -20°C to +100°C

Without O-ring: -60°C to +200°C

가 VAT

가 가 .

(15.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

	Article designation / size	, C mm	Thread length D mm	Ø (mm)	/ PU
SKINDICHT® BL-M					
52103100	M 12 x 1,5	7.5	5	14.0	100
52103110	M 16 x 1,5	8.0	5	18.0	100
52103120	M 20 x 1,5	9.5	6	22.0	100
52103130	M 25 x 1,5	11.0	7	28.0	100
52103140	M 32 x 1,5	12.0	8	35.0	50
52103150	M 40 x 1,5	13.0	9	44.0	25
52103160	M 50 x 1,5	15.0	9	54.0	10
52103170	M 63 x 1,5	16.0	10	70.0	10
52103190	M 75 x 1,5	17.0	11	80.0	1
52103100LF	M 12 x 1,5	7.5	5	14.0	100
52103110LF	M 16 x 1,5	8.0	5	18.0	100
52103120LF	M 20 x 1,5	9.5	6	22.0	100
52103130LF	M 25 x 1,5	11.0	7	28.0	100
52103140LF	M 32 x 1,5	12.0	8	35.0	50
52103150LF	M 40 x 1,5	13.0	9	44.0	25
52103160LF	M50x1,5	15.0	9	54.0	10
52103170LF	M63x1,5	16.0	10	70.0	10
52103190LF	M75x1,5	17.0	11	80.0	1
O- SKINDICHT® BL-M					
52103105	M 12 x 1,5	7.5	5	14.0	100
52103115	M 16 x 1,5	8.0	5	18.0	100
52103125	M 20 x 1,5	9.5	6	22.0	100
52103135	M 25 x 1,5	11.0	7	28.0	100
52103145	M 32 x 1,5	12.0	8	35.0	50
52103155	M 40 x 1,5	13.0	9	44.0	25
52103165	M 50 x 1,5	15.0	9	54.0	10
52103175	M 63 x 1,5	16.0	10	70.0	10
52103105LF	M 12 x 1,5	7.5	5	14.0	100
52103115LF	M 16 x 1,5	8.0	5	18.0	100
52103125LF	M 20 x 1,5	9.5	6	22.0	100
52103135LF	M 25 x 1,5	11.0	7	28.0	100
52103145LF	M 32 x 1,5	12.0	8	35.0	50

(15.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® BL-M

	Article designation / size	, C mm	Thread length D mm	Ø (mm)	/ PU
52103155LF	M 40 x 1,5	13.0	9	44.0	25
52103165LF	M 50 x 1,5	15.0	9	54.0	10
52103175LF	M63x1,5	16.0	10	70.0	10
52103195LF	M75x1,5	17.0	11	80.0	1

(15.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® BL-M



(15.05.2024)