

# SKINDICHT® HYGIENIC BL-M

SKINDICHT® HYGIENIC BL-M,

, 가 가

No gaps, voids or outer lying thread - so no risk of contamination of food machines, facilities or components



(30.04.2024)

# SKINDICHT® HYGIENIC BL-M

NSF/ANSI 169  
ECOLAB®

FDA 21 CFR 177.2600

DIN EN 1672-2

DIN EN ISO 14159  
Security of machinery – Hygienic requirements for the design of machinery

DIN EN 60423  
DIN IEC 62444

ETIM 5:	ETIM 5.0 Class-ID: EC000032
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000032
	ETIM 6.0 Class :
:	: - V4A (1.4404/316L) : FKM
가:	IP 68 - 10 bar
:	-20°C to +220°C

가 VAT 가 가 .

(30.04.2024)



# SKINDICHT® HYGIENIC BL-M

	Article designation / size	SW (mm)	, C mm	Thread length D mm	Ø (mm)	/ PU
52103490	M 12 x 1,5	16	16.9	6.5	18.8	5
52103491	M 16 x 1,5	20	17.9	7	22.8	5
52103492	M 20 x 1,5	24	19.9	8	26.8	5
52103493	M 25 x 1,5	29	20.7	8	31.8	5
52103488	M 32 x 1,5	36	22.5	9	39.6	5
52103489	M 40 x 1,5	45	23.5	9	49.0	5

(30.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16