

SKINDICHT® JT PTFE PG

SKINDICHT® JT PTFE PG, , PG , , , , , ,



, , , ,

PTFE , SKINTOP® SKINDICHT®

가 () 가 ,

ETIM 5:

ETIM 5.0 Class-ID: EC001181
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC001181
ETIM 6.0 Class :

:

PTFE

:

-120°C +250°C
: +300°C

(24.04.2024)



SKINDICHT® JT PTFE PG

가 VAT 가 가 .

(24.04.2024)



SKINDICHT® JT PTFE PG

	Article designation / size	Ø/ Ø (mm)	(mm)	Ø (mm)	/ PU
SKINDICHT® JT PTFE					
53801035	PG 7	12.5 / 16.5	2.0	16.5	100
53801045	PG 9	15.2 / 19.0	2.0	19.0	100
53801055	PG 11	18.6 / 22.5	2.0	22.5	100
53801065	PG 13,5	20.4 / 25.0	2.0	25.0	100
53801075	PG 16	22.5 / 27.0	2.0	27.0	100
53801085	PG 21	28.3 / 33.5	3.0	33.5	50
53801095	PG 29	37.0 / 43.5	3.0	43.5	50
53801105	PG 36	47.0 / 55.0	3.0	55.0	25
53801115	PG 42	54.0 / 63.0	3.0	63.0	25
53801125	PG 48	59.3 / 69.0	3.0	69.0	25

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16