


SKINDICHT® SRE

SKINDICHT® SRE, - (anti-kink) ,

PG



360°

가 (anti-kink) .

PG

: SKINDICHT® SM

EMC , SKINDICHT® SM ,

(24.04.2024)

SKINDICHT® SRE

Example order identification:

SRE 13.5 / 9 / 9 / 6

13.5 = PG thread compression screw

9 = PG connection thread

9 = Clear width of sealing cone

6 = Clear width earthing sleeve

ETIM 6:

:

:

:

가:

:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

T21

(thread)

가

: plain

: CR

O- : NBR

IP 65

-20°C +80°C

가 VAT

가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

	Article designation / size	Ø, / (mm)	/ Ø (mm)	SW1/SW2 mm	, C mm	Thread length D mm	/ PU
SKINDICHT® SRE							
52010780	13,5/9/9/6	7.5 / 9	4.5 / 6	22.0 / 22.0	60.0	5.5	25
52010790	13,5/9/11/7	9 / 11	5.5 / 7	22.0 / 22.0	60.0	5.5	25
52010800	13,5/11/9/6	7.5 / 9	4.5 / 6	22.0 / 22.0	60.0	5.5	25
52010810	13,5/11/11/7	9 / 11	5.5 / 7	22.0 / 22.0	60.0	5.5	25
52005310	13,5/13,5/9/6	7.5 / 9	4.5 / 6	22.0 / 22.0	60.0	6.5	25
52005320	13,5/13,5/11/7	9 / 11	5.5 / 7	22.0 / 22.0	60.0	6.5	25
52010820	16/11/13/9	11 / 13	7 / 9	24.0 / 24.0	65.0	5.5	25
52010830	16/11/13/10	11 / 13	8 / 10	24.0 / 24.0	65.0	5.5	25
52010840	16/11/15/11	13 / 15	9 / 11	24.0 / 24.0	65.0	5.5	25
52010850	16/13,5/13/9	11 / 13	7 / 9	24.0 / 24.0	67.0	6	25
52010860	16/13,5/13/10	11 / 13	8 / 10	24.0 / 24.0	67.0	6	25
52010870	16/13,5/15/11	13 / 15	9 / 11	24.0 / 24.0	67.0	6	25
52005330	16/16/13/9	11 / 13	7 / 9	24.0 / 24.0	65.0	6.5	25
52005340	16/16/13/10	11 / 13	8 / 10	24.0 / 24.0	65.0	6.5	25
52005350	16/16/15/11	13.5 / 15	9 / 11	24.0 / 24.0	65.0	6.5	25
52010880	21/16/15/12	13.5 / 15	10 / 12	30.0 / 30.0	78.0	6.5	25
52010890	21/16/17/14	15 / 17	12 / 14	30.0 / 30.0	78.0	6.5	25
52010900	21/16/19/15	17 / 19	13 / 15	30.0 / 30.0	78.0	6.5	25
52010910	21/16/20/16	18 / 20	14 / 16	30.0 / 30.0	78.0	6.5	25
52005360	21/21/15/12	13 / 15	10 / 12	30.0 / 30.0	78.0	7	25
52005370	21/21/17/14	15 / 17	12 / 14	30.0 / 30.0	78.0	7	25
52005380	21/21/19/15	17 / 19	13 / 15	30.0 / 30.0	78.0	7	25
52005390	21/21/20/16	18 / 20	14 / 16	30.0 / 30.0	78.0	7	25
52005400	29/29/20/17	19 / 20	15 / 17	40.0 / 41.0	90.0	8	10
52005410	29/29/23/19	22 / 23	17 / 19	40.0 / 41.0	90.0	8	10
52005411	36/36/26/22	23.5 / 26	20 / 22	50.0 / 50.0	109.0	9	5
52005412	36/36/30/24	27 / 30	22 / 24	50.0 / 50.0	109.0	9	5
52003585	36/36/30/26	27 / 30	24 / 26	50.0 / 50.0	109.0	9	5
52005414	36/36/33/28	30 / 33	26 / 28	50.0 / 50.0	109.0	9	5
52023586	36/36/35/30	32 / 35	28 / 30	50.0 / 50.0	109.0	9	5