


SKINDICHT® SHZ-M

SKINDICHT® SHZ-M, , 가



가

, , 가

DIN EN 60423

DIN IEC 62444

SKINDICHT® SHZ-M-XL SKINDICHT® SHZ-M , (thread)

: SKINDICHT® SM-M

:
SHZ-M 16/9
16 =
9 = PG

(23.04.2024)



SKINDICHT® SHZ-M

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

T21

:

:

: CR/NBR

O- : NBR

가:

IP 55

:

-20°C +80°C

가 VAT

가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® SHZ-M

	Article designation / size	Clamping range ØF mm	Ø F mm	(mm)	PG (thread)	SW1/SW2 mm	, C mm	Thread length D mm	F (mm)	/ PU
SKINDICHT® SHZ-M										
52106700	M 12 x 1,5	5.0 - 5.0	5.5 - 6.5	21	7	14 / 15	30.0	5	8.0	50
52106710	M 16 x 1,5	5.0 - 8.0	5.0 - 8.0	25	9	18 / 17	33.0	5	10.0	50
52106720	M 20 x 1,5	7.0 - 10.0	8.0 - 12.0	28	11	22 / 20	35.0	6	12.0	25
52106730	M 20 x 1,5	7.0 - 13.0	8.5 - 13.0	32	13.5	22 / 22	39.5	6	14.0	25
52106740	M 20 x 1,5	8.0 - 13.5	8.0 - 15.0	35	16	24 / 24	41.5	6	15.0	25
52106750	M 25 x 1,5	11.0 - 20.0	14.0 - 19.3	46	21	30 / 30	47.0	7	20.0	25
52106760	M 32 x 1,5	18.0 - 27.0	19.0 - 27.0	58	29	40 / 41	53.0	8	27.0	10
52106770	M 40 x 1,5	24.0 - 31.0	27.0 - 34.0	70	36	50 / 50	60.0	8	34.0	10
52106780	M 50 x 1,5	30.0 - 42.5	35.0 - 43.0	78	42	57 / 57	65.0	9	43.0	5
52106790	M 63 x 1,5	36.0 - 47.0	40.0 - 47.5	86	48	66 / 64	68.0	10	48.0	5
SKINDICHT® SHZ-M-XL										
52106705	M 12 x 1,5	5.0 - 5.0	5.5 - 6.5	21	7	14 / 15	35.0	10	8.0	50
52106715	M 16 x 1,5	5.0 - 8.0	5.0 - 8.0	25	9	18 / 17	38.0	10	10.0	50
52106725	M 20 x 1,5	7.0 - 10.0	8.0 - 12.0	28	11	22 / 20	39.0	10	12.0	25
52106735	M 20 x 1,5	7.0 - 13.0	8.5 - 13.0	32	13.5	22 / 22	43.5	10	14.0	25
52106745	M 20 x 1,5	8.0 - 13.5	9.0 - 14.5	35	16	24 / 24	45.5	10	15.0	25
52106755	M 25 x 1,5	11.0 - 20.0	14.0 - 19.3	46	21	30 / 30	51.0	11	20.0	25
52106765	M 32 x 1,5	18.0 - 27.0	19.0 - 27.0	58	29	40 / 41	58.0	13	27.0	10
52106775	M 40 x 1,5	24.0 - 31.0	27.0 - 34.0	70	36	50 / 50	67.0	13	34.0	10
52106785	M 50 x 1,5	30.0 - 42.5	35.0 - 43.0	78	42	57 / 57	70.0	14	43.0	5
52106795	M 63 x 1,5	36.0 - 47.0	40.0 - 47.5	86	48	66 / 64	73.0	14	48.0	5

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16