

SKINDICHT® RWV-M

SKINDICHT® RWV-M, , / ,



DIN EN 60423

DIN IEC 62444

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® RWV-M

: SKINDICHT® SM-M

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

:

,

:

: CR/NBR

O- : NBR

가:

IP 55

:

-20°C +100°C

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® RWV-M

	Article designation / size	Clamping range ØF mm	L	SW1	Ø A1	SW2	Ø A2	Ø G	(mm)	C mm	Thread length D mm	SW3	/ PU
SKINDICHT® RWV-M													
52107800	M 12 x 1,5	5.0	20.5	14.0	16	12.0	13.2	8.0	5.0	26.1	11.5	17	25
52107810	M 16 x 1,5	9.0 - 3.0	23.5	18.0	20	16.0	17.6	12.0	5.0	28.6	11.5	22	25
52107820	M 20 x 1,5	13.0 - 4.0	28.5	22.0	24	20.0	22.2	15.0	5.0	35.1	12.5	27	25
52107830	M 25 x 1,5	17.5 - 8.5	31	27.0	29	25.0	27.5	20.0	5.0	38.1	13.5	32	10
52107840	M 32 x 1,5	25.0 - 16.0	33.5	34.0	36	32.0	35.2	27.0	5.0	44.6	13.5	41	10
52107850	M 40 x 1,5	32.0 - 23.0	43	42.0	45	40.0	43.5	35.0	5.0	53.1	15.5	46	5