


SKINDICHT® SR-M

SKINDICHT® SR-M,

- (anti-kink)



가

VDE 0700-1

DIN EN 60423

DIN IEC 62444

: SKINDICHT® SM-M

EMC , SKINDICHT® SRE-M

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® SR-M

:
SR-M 12/7/5
12 =
7 = PG
5 =

ETIM 5:

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441
ETIM 6.0 Class :

:

T21

:

가

:

:
O- : NBR

: CR/NBR

가:

IP 65

:

-20°C +80°C

가 VAT 가 가 .

SKINDICHT® SR-M

	Article designation / size	Clamping range ØF mm	(mm)	(thread) PG	SW1/SW2 mm	, C mm	Thread length D mm	F (mm)	/ PU
SKINDICHT® SR-M									
52106410	M 12 x 1,5	4.0 - 5.0	23	7	14 / 15	49.0	5	5.0	50
52106420	M 16 x 1,5	5.5 - 7.0	25	9	18 / 17	50.0	5	7.0	50
52106430	M 20 x 1,5	5.5 - 7.0	28	11	22 / 20	55.0	6	7.0	25
52106440	M 20 x 1,5	7.5 - 9.0	28	11	22 / 20	55.0	6	9.0	25
52106450	M 20 x 1,5	7.5 - 9.0	32	13.5	22 / 22	60.0	6	9.0	25
52106460	M 20 x 1,5	9.0 - 11.0	32	13.5	22 / 22	60.0	6	11.0	25
52106470	M 20 x 1,5	11.0 - 13.0	32	13.5	22 / 22	60.0	6	13.0	25
52106480	M 20 x 1,5	12.0 - 13.0	35	16	24 / 24	65.0	6	13.0	25
52106481	M 20 x 1,5	13.0 - 15.0	35	16	24 / 24	66.0	6	15.0	25
52106490	M 25 x 1,5	12.5 - 15.0	46	21	30 / 30	78.5	7	15.0	25
52106500	M 25 x 1,5	14.0 - 17.0	46	21	30 / 30	78.5	7	17.0	25
52106510	M 25 x 1,5	17.0 - 19.0	46	21	30 / 30	78.5	7	19.0	25
52106520	M 25 x 1,5	17.0 - 20.0	46	21	30 / 30	78.5	7	20.0	25
52106530	M 32 x 1,5	19.0 - 20.0	59	29	40 / 41	90.5	8	20.0	10
52106540	M 32 x 1,5	22.0 - 23.0	59	29	40 / 41	90.5	8	23.0	10
52106550	M 32 x 1,5	23.0 - 25.0	59	29	40 / 41	90.5	8	25.0	10
52106560	M 40 x 1,5	24.0 - 26.0	70	36	50 / 50	108.0	8	26.0	5
52106570	M 40 x 1,5	28.0 - 30.0	70	36	50 / 50	108.0	8	30.0	5
52106580	M 40 x 1,5	31.0 - 33.0	70	36	50 / 50	108.0	8	33.0	5
52106590	M 40 x 1,5	33.0 - 34.5	70	36	50 / 50	108.0	8	35.0	5
52106600	M 50 x 1,5	31.0 - 34.5	75	42	57 / 57	111.0	9	35.0	5
52106610	M 50 x 1,5	32.0 - 38.0	75	42	57 / 57	111.0	9	38.0	5
52106620	M 50 x 1,5	37.0 - 40.0	75	42	57 / 57	111.0	9	40.0	5
52106630	M 63 x 1,5	32.0 - 40.0	83	48	66 / 64	118.0	10	40.0	1
52106640	M 63 x 1,5	36.0 - 44.0	83	48	66 / 64	118.0	10	44.0	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16