


SKINDICHT® SRE-M

SKINDICHT® SRE-M, - (anti-kink) ,

가



360°

가 (anti-kink)

DIN EN 60423

DIN IEC 62444

SKINDICHT® SM-PE-M

(24.04.2024)

SKINDICHT® SRE-M

Example description:

SRE-M 20/13.5/9/6

20 = metric connection thread

13.5 = PG function thread

9 = clear opening of anti-kink sleeve (F)

6 = clear opening of earthing sleeve (B)

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

T21

:

가

:

:

: plain

: CR

O- : NBR

가:

IP 65

:

-20°C +80°C

가 VAT 가 가 .

SKINDICHT® SRE-M

	Article designation / size	(thread) PG	Outer sheath clamping range ØF mm	(mm)	SW1/SW2 mm	, C mm	Thread length D mm	ØB	F (mm)	/ PU
SKINDICHT® SRE-M										
52105600	M 20 x 1,5	13.5	7.5 - 9	4.5 - 6	22 / 22	59.5	6	6	9.0	25
52105610	M 20 x 1,5	13.5	9 - 11	5.5 - 7	22 / 22	59.5	6	7	11.0	25
52105620	M 20 x 1,5	16	11 - 13	7 - 9	24 / 24	64.5	6	9	13.0	25
52105630	M 20 x 1,5	16	11 - 13	8 - 10	24 / 24	64.5	6	10	13.0	25
52105640	M 20 x 1,5	16	13.5 - 15	9 - 11	24 / 24	64.5	6	11	15.0	25
52105650	M 25 x 1,5	21	13.5 - 15	10 - 12	30 / 30	78.0	7	12	15.0	25
52105660	M 25 x 1,5	21	15 - 17	12 - 14	30 / 30	78.0	7	14	17.0	25
52105670	M 25 x 1,5	21	17 - 19	13 - 15	30 / 30	78.0	7	15	19.0	25
52105680	M 25 x 1,5	21	18 - 20	14 - 16	30 / 30	78.0	7	16	20.0	25
52105690	M 32 x 1,5	29	18 - 20	15 - 17	40 / 40	90.0	8	17	20.0	10
52105700	M 32 x 1,5	29	21 - 23	17 - 19	40 / 40	90.0	8	19	23.0	10
52105710	M 40 x 1,5	36	23.5 - 26	20 - 22	50 / 50	108.0	8	22	26.0	5
52105720	M 40 x 1,5	36	27 - 30	22 - 24	50 / 50	108.0	8	24	30.0	5
52105730	M 40 x 1,5	36	30 - 33	26 - 28	50 / 50	108.0	8	28	33.0	5
52105740	M 40 x 1,5	36	32 - 35	28 - 30	50 / 50	108.0	8	30	35.0	5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16