

SKINTOP® MS-HF-M BRUSH

SKINTOP® MS-HF-M BRUSH, nickel-plated brass cable gland with low resistance 360° screen contact, fast and simple assembling

Hazard Level: HL 3



CE UK CA



360°

(21.02.2024)

SKINTOP® MS-HF-M BRUSH

DIN EN 45545-2 (HL3)
DIN EN 45545-3 (E30)

DIN EN 60423
DIN IEC 62444

SKINDICHT® SM-PE-M

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

T21

:

Body: nickel plated brass

Insert: halogen-free polyamide acc. to UL 94 V0

EMC-brush: brass wire

Sealing: special elastomere

O-ring: special elastomere

가:

IP 68 - 5 bar

:

Dynamic: -25°C up to +100°C

: -40°C +100°C

가 VAT 가 가 .

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINTOP® MS-HF-M BRUSH

	Article designation / size	Ø F mm	(mm) Ø ,	SW (mm)	, C mm	Thread length D mm	/ PU
53112543	M 25 x 1,5	9 - 17	6	29	36.0	8	10
53112544	M 32 x 1,5	11 - 21	8	36	42.2	9	5
53112545	M 40 x 1,5	19 - 28	10	45	49.5	9	5
53112546	M 50 x 1,5	27 - 35	14	54	52.0	10	5
53112547	M 63 x 1,5	34 - 45	20	67	61.3	15	1

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16