

## SKINTOP® BS-SC-M METAL / SKINTOP® BSR-SC-M METAL

Brass cable gland with bending protection spiral for use on moving machine parts, optimum EMC protection due to highly conductive contact spring.

Permanent bending protection for EMC applications under high mechanical stress



CE UK  
CA



Bending protection spiral prevents excessive bending as well as kinking of the connected cable.

Special design of the stainless steel spiral allows high number of bending cycles.

Optimum EMC protection due to integrated, highly conductive and flexible contact spring, which creates a low-impedance transition between the copper shielding braid and the cable gland.

Large, variable clamping range for different cable outer diameters.

Best possible sealing by O-ring and sealing ring enables protection class IP 68 (10 bar) and IP 69.

For EMC-compliant insertion of copper-shielded cables.

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



SKINTOP® BS-SC-M METAL / SKINTOP® BSR-SC-M METAL

Especially on moving machine parts.  
Withstands high mechanical loads.  
Suitable for outdoor use.

DIN EN 60423  
DIN IEC 62444

Variant "R" with reduction sealing insert for sealing smaller diameter pipes.

ETIM 5:	ETIM 5.0 Class-ID: EC000441
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000441
	ETIM 6.0 Class :
:	T21
:	:
	:
	: CR
	O- : NBP

가:	IP 68 - 10 bar
	IP 69
:	Dynamic: -25°C up to +100°C
	Fixed: -30°C up to +100°C

가 VAT 가 가 .



SKINTOP® BS-SC-M METAL / SKINTOP® BSR-SC-M METAL

	Article designation / size	Ø (mm), from - to	(mm) Ø	SW (mm)	Thread length D mm	/ PU
53806825	M 12 x 1,5	3.5 - 7.0	1	16	6.5	25
53806826	M 16 x 1,5	4.5 - 10.0	4	20	7	25
53806827	M 20 x 1,5	7.0 - 13.0	5	24	8	25
53806828	M 25 x 1,5	9.0 - 17.0	7.5	29	8	25
53806829	M 12 x 1,5	2.0 - 5.0	1	16	6.5	25
53806830	M 16 x 1,5	2.0 - 7.0	4	20	7	25
53806831	M 20 x 1,5	5.0 - 10.0	5	24	8	25
53806832	M 25 x 1,5	6.0 - 13.0	7.5	29	8	25

(01.05.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

SKINTOP® BS-SC-M METAL / SKINTOP® BSR-SC-M METAL



(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16