

# ETHERLINE® ACCESS PN IP67

PROFINET switch for decentralised applications

IP 67  
compatible for PROFINET®  
networks



Lapp



With 8 ports (10/100Base-T(X)) for D-coded M12 connectors.  
Particularly suitable for harsh environments thanks to protection class IP 67.  
Prioritisation of PROFINET telegrams with real-time data.  
Easy configuration and diagnostics via PROFINET or web interface.  
Supports MRP (client), LLDP, DCP, SNMP, allows port mirroring, diagnostic alarms and detailed network statistics.

For use in PROFINET networks in automation technology ("Conformance Class B").  
For decentralised use at field level, outside the control cabinet.  
Can be used in an extended temperature range from -40 °C to +75 °C.

power supply:	DC 24 V (18-30 V DC)
가:	IP 67
:	-40°C ~ +75°C

(24.04.2024)



# ETHERLINE® ACCESS PN IP67

PROFINET® PNO (PROFIBUS ) .

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



ETHERLINE® ACCESS PN IP67

Article number
21700147

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16