

SKINTOP® INOX SC NPT

SKINTOP® INOX / SKINTOP® INOX-R,

EMC



(24.04.2024)



SKINTOP® INOX SC NPT

- , EMC

EMC

EMC

(,)

ECOLAB®

DIN EN 1672-2

DIN EN ISO 14159

Security of machinery – Hygienic requirements for the design of machinery
NSF/ANSI 169

ASME B1.20.1 - 2013

NPT

ETIM 5:

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441
ETIM 6.0 Class :

:

Body: stainless steel V4A
(1.4404 / 316L)
Insert: polyamide
Sealing: silicone
O-Ring: silicone

가:

UL50E NEMA 1, 2, 4X, 6, 12
IP 68 - 5 bar

:

-40°C ~ +100°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINTOP® INOX SC NPT

	Article designation / size	Ø F mm	SW (mm)	, C mm	Thread length D mm	/ PU
53806818	NPT 1/4"	4 - 7	16	37.8	15	5
53806819	NPT 3/8"	6 - 10	20	40.4	15	5
53806820	NPT 1/2"	7 - 13	24	42.5	15	5
53806821	NPT 3/4"	9 - 17	29	46.2	15	5
53806822	NPT 1"	11 - 21	36	50.6	15	5
53806823	NPT 1 1/4"	19 - 28	45	59.2	17	5
53806824	NPT 1 1/2"	27 - 35	54	63.2	17	5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16