

ETHERLINE® ACCESS U IP67

Unmanaged industrial Ethernet switch for decentralised applications.

IP 67
compatible for PROFINET®
networks



Lapp



With 8 ports (10/100Base-T(X)) for D-coded M12 connectors.
Particularly suitable for harsh environments thanks to protection class IP 67.
Quickly ready for use with little installation effort.
High performance due to generous 16K MAC address table and extensive 256Kbyte packet buffer.

For use in Ethernet-based automation technology networks.
Also suitable for use in PROFINET networks ("Conformance Class A").
For decentralised use at field level, outside the control Cabinet.
Can be used in an extended temperature range from -40 °C to +75 °C.

power supply:	DC 24 V (18-30 V DC)
가:	IP 67
:	-40°C ~ +75°C

(24.04.2024)



ETHERLINE® ACCESS U IP67

PROFINET® PNO (PROFIBUS) .

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® ACCESS U IP67

Article number
21700148

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16