

ETHERLINE® FIRE

120 , 1Gbit/s

insulation integrity for at least 120 minutes in the event of fire



120

(EN50200)

가 가

- Fire behaviour:
- Halogen-free (IEC 60754-1 & EN50267-2-1)
 - Flame-retardant (IEC 60332-1)
 - Fire retardant (IEC 60332-3-24)
 - Low smoke density (IEC 61034-2)

(23.04.2024)

ETHERLINE® FIRE

Circuit integrity for data cables PH120 (120 minutes) acc. to EN 50289-4-16

: 2 () 4
FRNC , : (RAL3000)

ETIM 5: ETIM 5.0/6.0 Class-ID: EC000830
ETIM 5.0/6.0 Class :

ETIM 6: ETIM 6.0 Class-ID: EC000830
ETIM 6.0 Class :

: () 125 V
: : 15 x
.: 100 IEC 61156-5
: : -20 ~ 70°C

가 : EUR 100 , 150 kg. 가 가 (.) 가 .
가 가 / T17

가 VAT 가 가 .

(23.04.2024)



ETHERLINE® FIRE

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170905	ETHERLINE® FIRE Cat.5e PH120	4 x 2 x AWG23/1	0.95	8.6	24	75
2170913	ETHERLINE® FIRE Cat.6 PH120	4 x 2 x AWG22/1	1.5	10.2	48	145

(23.04.2024)



©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® FIRE



(23.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16