

# ETHERLINE® EC FD Cat.5e M8


EC M8

Industrial Ethernet Patchcord, EtherCat, Cat.5e, plug M8, PUR, for drag chain applications

가

[www.lappgroup.com/assemblyfinderor](http://www.lappgroup.com/assemblyfinderor)

2170433







Lapp



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ETHERLINE® EC FD Cat.5e M8

Connecting cable assembled on one or on both sides saves installation time and reduces or eliminates the potential for on-site assembly errors.

High resistance to electromagnetic interference thanks to star quad stranding as well as double shielding made of aluminium-laminated foil and a high degree of coverage (SF/UTP).

Available with RJ45, M8 or M12D connectors. The slim RJ45 connector enables use in devices with a very high port density, while the integrated vibration protection of the M8/M12D connector is useful for applications with shock and vibrations.

The angled shape of the connector is suitable for the space-saving cable outlet.

Halogen-free core insulation and sheath compound to meet special fire protection requirements.

Cable design enables highly flexible, constantly flexing use in moving machine parts and in the cable chain.

Also suitable for EtherCAT and EtherNET/IP applications.

Compliant with standards for use in buses (fire behaviour test according to UNECE-R 118 for vehicles of category M3 (II and III)).

The PUR outer sheath and connectors withstand high mechanical loads.

The PUR outer sheath is insensitive to mineral oil-based lubricants and is chemically resistant in many cases.

Cat.5e class D  
2 : , 10/100Mbit/s

Braided conductor, 2x2x AWG26/19

PUR : (RAL 6018 )  
M8 가

ETIM 5:	ETIM 5.0 Class-ID: EC002599
	ETIM 5.0 class : ( )
ETIM 6:	ETIM 6.0 Class-ID: EC002599
	ETIM 6.0 Class :
	Flexing: 16 x
	: 4 x
가:	M8 - IP67
	: -30 ° C ~ + 50 ° C
	: -40°C +80°C

가 VAT 가 가 . ( . ) 가 .  
가 가 가 .

(24.04.2024)



ETHERLINE® EC FD Cat.5e M8

Article number		(m)	kg/1.000 pieces
M8	M8		
2171700	IE-EC-5-M8-S-0,5-P-2-26-FD-M8-S	0.5	10
2171701	IE-EC-5-M8-S-1-P-2-26-FD-M8-S	1	20
2171702	IE-EC-5-M8-S-2-P-2-26-FD-M8-S	2	40
2171703	IE-EC-5-M8-S-3-P-2-26-FD-M8-S	3	60
2171704	IE-EC-5-M8-S-5-P-2-26-FD-M8-S	5	100
2171705	IE-EC-5-M8-S-7-P-2-26-FD-M8-S	7	140
2171706	IE-EC-5-M8-S-10-P-2-26-FD-M8-S	10	200
2171707	IE-EC-5-M8-S-15-P-2-26-FD-M8-S	15	300
2171708	IE-EC-5-M8-S-20-P-2-26-FD-M8-S	20	400
M8	M8		
2171718	IE-EC-5-M8-A-0,5-P-2-26-FD-M8-S	0.5	10
2171719	IE-EC-5-M8-A-1-P-2-26-FD-M8-S	1	20
2171720	IE-EC-5-M8-A-2-P-2-26-FD-M8-S	2	40
2171721	IE-EC-5-M8-A-3-P-2-26-FD-M8-S	3	60
2171722	IE-EC-5-M8-A-5-P-2-26-FD-M8-S	5	100
2171723	IE-EC-5-M8-A-7-P-2-26-FD-M8-S	7	140
2171724	IE-EC-5-M8-A-10-P-2-26-FD-M8-S	10	200
2171725	IE-EC-5-M8-A-15-P-2-26-FD-M8-S	15	300
2171726	IE-EC-5-M8-A-20-P-2-26-FD-M8-S	20	400
2171709	IE-EC-5-M8-S-0,5-P-2-26-FD-OE	0.5	10
2171710	IE-EC-5-M8-S-1-P-2-26-FD-OE	1	20
2171711	IE-EC-5-M8-S-2-P-2-26-FD-OE	2	40
2171712	IE-EC-5-M8-S-3-P-2-26-FD-OE	3	60
2171713	IE-EC-5-M8-S-5-P-2-26-FD-OE	5	100
2171714	IE-EC-5-M8-S-7-P-2-26-FD-OE	7	140
2171715	IE-EC-5-M8-S-10-P-2-26-FD-OE	10	200
2171716	IE-EC-5-M8-S-15-P-2-26-FD-OE	15	300
2171717	IE-EC-5-M8-S-20-P-2-26-FD-OE	20	400
Angled connector on free conductor end			
2171727	IE-EC-5-M8-A-0,5-P-2-26-FD-OE	0.5	10
2171728	IE-EC-5-M8-A-1-P-2-26-FD-OE	1	20
2171729	IE-EC-5-M8-A-2-P-2-26-FD-OE	2	40
2171730	IE-EC-5-M8-A-3-P-2-26-FD-OE	3	60

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ETHERLINE® EC FD Cat.5e M8

Article number		(m)	kg/1.000 pieces
2171731	IE-EC-5-M8-A-5-P-2-26-FD-OE	5	100
2171732	IE-EC-5-M8-A-7-P-2-26-FD-OE	7	140
2171733	IE-EC-5-M8-A-10-P-2-26-FD-OE	10	200
2171734	IE-EC-5-M8-A-15-P-2-26-FD-OE	15	300
2171735	IE-EC-5-M8-A-20-P-2-26-FD-OE	20	400

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ETHERLINE® EC FD Cat.5e M8



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16