


# ETHERLINE® MARINE FRNC FC CAT.5

Cat.5 , GL DNV FRNC , PROFINET - 100Mbit

가  
CAT.5-



2 : , 10/100Mbit/s

EtherCAT EtherNet/IP

100Mbit/s : 85m

(23.04.2024)



# ETHERLINE® MARINE FRNC FC CAT.5

(FC)

UL/CSA CM-Listing  
c(UL)us Typ PLTC acc. to UL 13  
IEC 60332-3

Colour-coded in accordance with PROFINET for Cat.5e applications

: 가 (FRNC)  
SF / UTP :  
: (RAL 6018 )

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	( ) 125 V
:	: 3 x
:	: 7.5 x
::	100 IEC 61156-5
:	: -25°C~+70°C
:	: 0 °C to +50 °C

가 : EUR 100 , 150 kg. 가 가 . ( . ) 가 .  
PROFINET® PNO (PROFIBUS ) . T17 .  
가 가 . /  
가 VAT 가 가 .



ETHERLINE® MARINE FRNC FC CAT.5

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170889	ETHERLINE® MARINE FRNC FC CAT.5	2 x 2 x AWG22/7	1.5	6.5	32	68

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16