



# ETHERLINE® PN Cat.5 FD

Cat.5 , PROFINET- Type C  
 2x2xAWG22/7  
 UL-

PROFINET  
 CAT.5-



가

2 : , 10/100Mbit/s

( )  
 EtherCAT EtherNet/IP

# ETHERLINE® PN Cat.5 FD

PUR ( )

UL/CSA CMX (UL 444)  
, UL VW1/CSA FT1  
VDE 0472-815

Colour-coded in accordance with PROFINET for Cat.5e applications

: 가 (FRNC)  
:  
PUR ,  
: (RAL 6018 )

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	( ) 125 V
:	8 x
:	Core/core: 700 V
	Core/screen: 700 V
..	100 IEC 61156-5
:	: -30°C +70°C
	: -20°C +60°C

가 : EUR 100 , 150 kg. 가 가 ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
PROFINET® PNO (PROFIBUS ) .  
가 . /  
가 VAT 가 가 .



# ETHERLINE® PN Cat.5 FD

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170894	ETHERLINE® FD P FC CAT.5	2 x 2 x AWG22/7	1.5	6.5	31.3	61

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16