


ETHERLINE® Cat.5 ARM

Cat.5 PROFINET

가

Type C, PE

CAT.5-



Lapp



EMC

2 : , 10/100Mbit/s

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® Cat.5 ARM

, UV

PROFINET C()
EtherCAT EtherNet/IP

(FC)

: PE

Colour-coded in accordance with PROFINET for Cat.5e applications

SF / UTP :

PVC (RAL6018)

2

(PE)

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

: () 125 V

: : 15 x

: 10 x

: Core/core: 2000 V

Core/screen: 2000 V

.: 100 IEC 61156-5

: : -20°C to +60°C

: -40°C +70°C

가 : EUR 100 , 150 kg. 가 가 . (.) 가 .
T17

www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

PROFINET® PNO (PROFIBUS)

가 . /

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® Cat.5 ARM

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170496	ETHERLINE® Cat.5 ARM	2 x 2 x AWG22/1	1.5	6.5 / 9.3	30.4	124

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16