


ETHERLINE® TORSION Cat. 5

Cat 5, class D
 Cat.5 (±180°), 2, AWM PUR, PROFINET 2x2xAWG22/19

, 2 ,
 PROFINET
 CAT.5-



Lapp



가

2 : , 2 ,
 , 10/100Mbit/s

(24.04.2024)



ETHERLINE® TORSION Cat. 5

(: PROFINET – ,가 TORSION)

EtherCAT EtherNet/IP

(180° /)

PUR

UL AWM (Style 21161)
VDE 0472-815
IEC 60332-1-2

AWG 22 (19-wire)
: PE

:

PUR , (RAL 6018)

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	. 100 V ()
:	5 x
:	700 V
∴	100 IEC 61156-6
:	-40°C +80°C

가 : EUR 100 , 150 kg. 가 가 . (.) 가 . T17

www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

PROFINET® PNO (PROFIBUS)

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® TORSION Cat. 5

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170888	ETHERLINE® TORSION CAT.5	2 x 2 x AWG22/19	1.5	6.5	31.3	52

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16