


# ETHERLINE® Y CAT.5e BK

Industrial Ethernet cable Cat.5 for special applications, for PROFINET application Type C design 2x2xAWG22/7, PVC jacket

PROFINET  
CAT.5-



Lapp



UV

가

2 : , UV

, 10/100Mbit/s

Many applications with Industrial Ethernet, e.g. PROFINET type C, i.e. fixed installation and flexible use.

EtherCAT EtherNet/IP

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ETHERLINE® Y CAT.5e BK

EN 50363-4-1 PVC TM2

IEC 60332-1-2

7-가 ,

Colour-coded in accordance with PROFINET for Cat.5e applications

:  
PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	( ) 125 V
:	: 10 x
	: 15 x
:	/ : 1000 V
	/ : 500 V
::	100 IEC 61156-5
:	: -10°C +70°C
	: -40°C +80°C

가 : EUR 100 , 150 kg. 가 가 . ( . ) 가 .  
 www.lappkabel.de/en/cable-standradlengths T17  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 PROFINET® PNO (PROFIBUS ) .

가 VAT 가 가 .

(24.04.2024)



## ETHERLINE® Y CAT.5e BK

		AWG	(mm)	(mm)	(kg/km)	(kg/km)
2170901	ETHERLINE® Y CAT.5e BK	2 x 2 x AWG22/7	6.2	1.5	30.4	59

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16