


# ETHERLINE® PN Cat.6A FLEX

Cat.6A, 4, UL PVC FRNC, 4x2xAWG23/7

PROFINET (4)  
CAT.6<sub>A</sub> qualified for 10Gbit/s



Lapp



가

4 : 100Mbit/s ~ 10Gbit/s

EN 50173-3 ISO/IEC 24702 2 3

(24.04.2024)



# ETHERLINE® PN Cat.6A FLEX

EtherCAT EtherNet/IP  
(7 가 )

가 CAT.6A, 10Gbit/s  
CAT.6A, ISO/IEC 11801 EN 50173  
, PVC 가

UL approvals see data sheet  
ETHERLINE® PN CAT.6 Y FLEX FC : ECOLAB®

7-가  
: PE  
S/FTP:  
PVC FRNC  
: (RAL 6018 )

ETIM 5:	ETIM 5.0/6.0 Class-ID: EC000830
	ETIM 5.0/6.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	( ) 125 V
:	( ) : 15 x
:	: 8 x
..	100 IEC 61156-5
:	FRNC 가 : -25°C ~ +80°C
	: -10°C to +80°C PVC 가 :
	-40°C ~ +80°C : -10°C ~ +70°C

PROFINET® PNO (PROFIBUS 가 ) 가 . ( . ) 가 .  
가 VAT 가 가 .



# ETHERLINE® PN Cat.6A FLEX

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
PVC						
2170930	ETHERLINE PN Cat.6 <sub>A</sub> Y FLEX	4 x 2 x AWG23/7	1.5	8.8	48	92
FRNC						
2170931	ETHERLINE PN Cat.6 <sub>A</sub> FRNC FLEX	4 x 2 x AWG23/7	1.5	8.8	48	87

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## ETHERLINE® PN Cat.6A FLEX



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16