


# ETHERLINE® LAN 1000 Cat. 7A

Cat 7A/ class FA - 1000MHz

Category 7A/ class FA - 1000MHz

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



EN 50173 ISO/IEC 11801

LAN

가  
3  
3  
90 m + ( 10 m ) ( ) ISO/IEC 11801 EN 50173 ,100 m . (

IEEE 802.3: 10/100/1000Base-T, 10GBase-T IEEE 802.5: ISDN; FDDI; ATM;

IEEE 802.3at: PoE, VoIP

Lapp Kabel LAN CAT.5e EIA/TIA-568 TSB36 ISO/IEC 11801 EN 50173 ( FA - )  
2170980/ 2170981  
Flame-retardant according to IEC 60332-1-2  
LSZH ,IEC 60332-1-2, UL FT-2  
IEC 60332-3-25 ( )

(24.04.2024)



# ETHERLINE® LAN 1000 Cat. 7A

4x2xAWG23/1,  
 2x (4x2xAWG23)  
 : PE  
 S/FTP:  
 :  
 : (RAL 7032)

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

:

: 4 x

: 8 x

::

100 ± 15%

:

: 0 °C to +50 °C

: -20°C ~+60°C

:

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



ETHERLINE® LAN 1000 Cat. 7A

Article number		AWG	(mm)	mm		(kg/km)	(kg/km)
ETHERLINE® LAN 1000 Cat.7A 4x2xAWG23							
2170980	ETHERLINE LAN 1000 Cat.7A 4x2x23AWG	4 x 2 x AWG23/1	1.3	7.2		30	50
2170981	ETHERLINE LAN 1000 Cat.7A 2x(4x2x23AWG)	2x(4x2x23AWG)	1.3	14.8		60	101
ETHERLINE® LAN 1000 Cat.7A 4x2xAWG23 LSZH							
2170971	ETHERLINE® LAN 1000 Cat.7A 4x2xAWG23 LSZH	4 x 2 x AWG23/1	1.3	7.5		30	56
2170972	ETHERLINE® LAN 1000 Cat.7A 2x(4x2xAWG23) LSZH duplex	2x (4x2xAWG23/1)	1.3	15.2		60	113

(24.04.2024)




©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ETHERLINE® LAN 1000 Cat. 7A



(24.04.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16