


# ETHERLINE® TORSION Cat.7

4 , PROFINET Type C Cat.7 UL (±180°) PUR , 4x2xAWG24/7

(± 180°)  
 PROFINET (4 )  
 10Gbit/s CAT.7



Lapp



(24.04.2024)

# ETHERLINE® TORSION Cat.7



4 : ( : PROFINET – , 가 TORSION )  
100Mbit/s ~ 10Gbit/s

EN 50173-3 ISO/IEC 24702 2 3

EtherCAT EtherNet/IP

IEC 60754-1  
ACC. IEC 60811-2-1

5

180° /

IEC 61156-6  
UL/CSA (CMX)  
UL AWM 21576  
: IEC 60332-1-2

7-가

(PE)

SF/FTP: Aluminium compound foil and copper braid as overall screening and pair screening with aluminium compound foil  
PUR

: (RAL 6018 )

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

:

( ) 125 V

:

: 8 x

: 15 x

∴

100 ± 5 Ohm (> 1 MHz)

:

: -40°C bis +80°C

: -30°C +70°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## ETHERLINE® TORSION Cat.7

가 VAT 가 가 .  
UL-Zertifizierungen sind dem Datenblatt zu entnehmen

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## ETHERLINE® TORSION Cat.7

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170481	ETHERLINE® TORSION CAT.7	4x2xAWG24/7	1.4	9.4	44	95

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16