

UNITRONIC® BUS CAN BURIAL

/ CAN
CAN ISO 11898 , , . : -40 ° ~ + 80 °C



Lapp



ISO 11898 CAN
- , 가
(), UV-

CANopen CAN 가

UNITRONIC® BUS CAN BURIAL

7x0.32
: PE
: PVC, RAL(4001), : 7.1 mm
: PE, RAL(9005), : 9.0 mm

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	(1kHz): 40nF/km
:	300 V ()
:	(): 74Ohm/km
:	: 8 x
:	: 4 x
:	/ : 1500 V
..	120 ohm
:	: -40°C +80°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: ≤ 30 kg or ≤ 250 m, . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

UNITRONIC® BUS CAN BURIAL

		(CORE) / (mm ²)	(mm)	[kg/km]	[kg/km]
2170500	UNITRONIC BUS CAN BURIAL 4x1x0,5	4 x 1 x 0.5	9	41.8	91

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16