


# UNITRONIC® BUS CAN FD P

CAN - UL/SCA

CAN CAN . , . IEC 60332-1-2, : -40 °C + 80 °C



LAPP KABEL STUTTGART UNITRONIC® BUS CAN FD P



: 1 Mbit/s 40 m

ISO 11898 가 ( ISO 11898).  
: IEC 60332-1-2

ISO 11898  
UL/CSA CMX (UL 444)

(23.04.2024)

# UNITRONIC® BUS CAN FD P

:  
 : PUR, (RAL 4001)  
 UV- ( , )

ETIM 6:	ETIM 6.0 Class-ID: EC000830
:	ETIM 6.0 Class :
:	(800 Hz) max. 40 nF/km
:	250 V ( )
:	( ): . 159.8 ohm/km
:	: 15 x
:	/ : 1500 V
∴	120 ohm
:	: -40°C +80°C
	: -30°C +70°C

, 가 가 . ( . ) 가 .  
 www.lappkabel.de/en/cable-standradlengths  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(23.04.2024)



# UNITRONIC® BUS CAN FD P

		/ / (mm <sup>2</sup> )	(mm)		(kg/km)	(kg/km)
	( , )					
2170272	UNITRONIC® BUS CAN FD P	1 x 2 x 0.25	6.4	159.8	24	40
2170273	UNITRONIC® BUS CAN FD P	2 x 2 x 0.25	8.4	159.8	33	65
2170275	UNITRONIC® BUS CAN FD P	1 x 2 x 0.34	6.8	122	32.8	60
2170276	UNITRONIC® BUS CAN FD P	2 x 2 x 0.34	9.6	122	52.4	88
2170278	UNITRONIC® BUS CAN FD P	1 x 2 x 0.5	8	72.8	41.9	74
2170279	UNITRONIC® BUS CAN FD P	2 x 2 x 0.5	10.1	72.8	59.4	100

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16