

UNITRONIC® BUS CAN TRAY

PLTC-ER CAN -

NEC PLTC-ER PLTC-ER , UV , . : -40 °C ~ + 80 °C

CAN = Controller Area Network



NEC 725.154 (D) / ACC PLTC-ER .

가 가

: 1 Mbit/s 40 m

ISO 11898

(25.04.2024)



UNITRONIC® BUS CAN TRAY

UV UL SUN RES
 UL OIL RES I
 CSA FT4 UL

ISO 11898
UL 444 / CSA 22.2 c(UL)us Typ CMG (75°C)
UL PLTC-ER . UL 13

7-가

:
: PVC
: PVC, (RAL 4001)

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	(800 Hz) max. 40 nF/km
:	() 250 V
	: 600 V (UL)
:	(loop): max. 110,8 ohm/km
:	: 8 x
	: 15 x
:	Core/core: 2000 V
.:	120 ohm
:	: -40°C +80°C
	: -10°C +70°C

 , 가 가 . (.) 가 .
 : www.lappkabel.de/en/cable-standradlengths
 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



UNITRONIC® BUS CAN TRAY

		(CORE) / (mm ²)	(mm)	[kg/km]	[kg/km]
2170857	UNITRONIC® BUS CAN TRAY	2 x 2 x 0.34	7.5	35	81

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16