

UNITRONIC® DeviceNet THICK + THIN

CAN DeviceNet

DeviceNet
-25 °C ~ + 80 °C

PLC

. Germanischer Lloyd UL / CSA . :



DeviceNet™ . (. , , , , , , PLCs)

CAN ()
가
FRNC : ,

CMG UL / CSA 75 ° C PLTC, Sun Res.
FRNC variant additionally with

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® DeviceNet THICK + THIN

DNV GL certification
 DNV GL certificate no. TAE00001JE

:
 : (FRNC)
 (PVC)

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	: +
:	: +
:	(800 Hz): . 39.8 nF/km
:	300 V ()
:	(): . 45 ohm/km
:	(): . 180 ohm/km
:	: 15 x
:	Core/core: 2000 V
..	120 ohm
:	: -25°C +80°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 FRNC Flame-Retardant (), Non-Corrosive () ; DeviceNet ODVA .
 Lapp Kabel PROFIBUS user organisation (PNO)
 ECO 2170342 2017343 가 UL/CSA
 (CMG)
 가 VAT 가 가 .



UNITRONIC® DeviceNet THICK + THIN

		() x AWG	(mm)	[kg/km]	[kg/km]
2170340	UNITRONIC® BUS DN THICK FRNC	1x2xAWG18 + 1x2xAWG15	12.2	82.8	195
2170341	UNITRONIC® BUS DN THIN FRNC	1x2xAWG24 + 1x2xAWG22	6.9	33.4	69.5
PVC					
2170342	UNITRONIC® BUS DN THICK Y	1x2xAWG18 + 1x2xAWG15	12.2	88.4	192
2170343	UNITRONIC® BUS DN THIN Y	1x2xAWG24 + 1x2xAWG22	6.9	33.4	66.9

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16