

UNITRONIC® BUS CAN M12

DeviceNet / CAN open : M12 /

PUR () DeviceNet M12 (A) ()

www.lappgroup.com/assemblyfinder 가



DeviceNet CANopen



Lapp



/
Space-saving due to compact dimensions.

5- DeviceNet/CANopen ,
- M12 A-

UNITRONIC® BUS CAN M12

UL-AWM-Style 21198 (80 °C / 300 V)

: 2 x 0.25 mm² : 2 x 0.34 mm² : 1 x 0.34 mm²
 : / , /
 () : PUR , /
 : 6.7 mm

ETIM 5:

ETIM 5.0 Class-ID: EC001855

ETIM 5.0 Class: -

ETIM 6:

ETIM 6.0 Class-ID: EC001855

ETIM 6.0 Class :

: CuSn : Ni/Au ,
: TPU, ,

가:

IP65/IP67

():

Plug/socket -25°C to +90°C
Fixed installation -40°C to +80°C
Flexing -20°C to +70°C

: A-Standard

(A):

4 A

가 VAT 가 가 . (.) 가 .

UNITRONIC® BUS CAN M12

		(m)	/	Design	(V)	PU
22260789	AB-DN-M12MS-2,0PUR	2	5		60	1
22260790	AB-DN-M12MS-5,0PUR	5	5		60	1
22260791	AB-DN-M12MS-10,0PUR	10	5		60	1
22262004	AB-DN-M12MA-2,0PUR	2	5		60	1
22260792	AB-DN-2.0PUR-M12FS	2	5		60	1
22260793	AB-DN-5.0PUR-M12FS	5	5		60	1
22260794	AB-DN-10.0PUR-M12FS	10	5		60	1

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16