

# UNITRONIC® BUS CC FD P FRNC

CC

- UL

CC-Link  
80 °C

. UV , , AWM 300V. : -40 °C ~ +

Lapp

CC-Link

(CLPA)



Lapp



CC-Link®

CC-Link® (Control & Communication Link) = BUS

( , )

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# UNITRONIC® BUS CC FD P FRNC

156 kbit/s 1.200 m  
625 kbit/s 900 m  
2,5 Mbit/s 400 m  
5,0 Mbit/s 160 m  
10 Mbit/s 100 m

: IEC 60332-1-2

AWM 20233 80 °C 300V

: PE  
: FRNC  
: PUR, (RAL 3000)

ETIM 5: ETIM 5.0 Class-ID: EC000830  
ETIM 5.0 Class- :  
ETIM 6: ETIM 6.0 Class-ID: EC000830  
ETIM 6.0 Class :  
: UL AWM Style 20233  
: 300 V  
: 11 ohm/1,000 ft. (305 m) at 20°C  
: : 4 x  
: 10 x  
: 2000 V  
.: 110 ohm at 1 MHz  
: -40°C +80°C

가 가 ( . ) 가  
www.lappkabel.de/en/cable-standradlengths  
CC-Link® CC-Link Partner Association, Japan (CLPA)

가 VAT 가 가 .



# UNITRONIC® BUS CC FD P FRNC

|         |                                | ( ) x AWG     | (mm) | (kg/km) | (kg/km) |
|---------|--------------------------------|---------------|------|---------|---------|
| 2170370 | UNITRONIC® BUS CC FD P<br>FRNC | 3 x 1 x AWG20 | 8.5  | 39.9    | 84      |

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16