



# UNITRONIC® BUS PB FESTOON

가 PROFIBUS

PROFIBUS-DP, PROFIBUS-FMS FIP , UL/CSA (CM, CL3, SUN RES, Oil Res I), CSA FT4  
UL, UL OIL RES I

LAPP KABEL STUIGART UNITRONIC® BUS PB FESTOON



PROFIBUS-FMS FIP PROFIBUS-DP  
CL3

PROFIBUS DP.(SIEMENS SIMATIC® NET, FIP 가 : DIN 19245 EN 50170 , )

FESTOON: (festoon)  
PNO

( A, PROFIBUS-DP):

93.75 kbit/s = 1200 m

187.5 kbit/s = 1000 m

500 kbit/s = 400 m

1.5 Mbit/s = 200 m

12.0 Mbit/s = 100 m

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# UNITRONIC® BUS PB FESTOON

UL/CSA (CM, CL3, SUN RES, Oil Res I)  
CSA FT4 UL  
UL OIL RES I

: PVC

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	(800 Hz): max. 30 nF/km
:	600 V ( )
:	: 70 mm
	: 30 mm once
:	Core/core: 2000 V
..	150 ± 15 Ohm
:	: -5°C +70°C
	: -40°C +80°C

가 가 ( ) 가 .  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 SIMATIC® SIEMENS AG . FIP World FIP .  
 Lapp Kabel PROFIBUS user organisation (PNO)  
 가 VAT 가 가 .



# UNITRONIC® BUS PB FESTOON

		(CORE) / (mm <sup>2</sup> )	(mm <sup>2</sup> )	(mm)	[kg/km]	[kg/km]
2170338	UNITRONIC® BUS PB Festoon CM	1 x 2 x 0.64	1 x 2 x 0.64	8	26	64

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16