

UNITRONIC® BUS IS

가 ISOBUS

°C

. ISO 11783-2 : 2012 .

-40 °C ~ + 85

AEF -



HYBRID:

+

ISOBUS

. (ISO 11783-2).

IEC 60332-1

UV-

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® BUS IS

PUR()

ISO 11783-2:2012

4x 0.5mm² (5(IEC 60228)) 가 가

2x 2,5mm² (,)

2x 6mm² (,)

: PUR PVC, (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

:

60V

:

: 10 x

: 15 x

:

0,5 mm~2,5 mm² / = 1,5kV,

6~10mm² / = 2,5kV

∴

Characteristic impedance: 75 ohm

:

PUR: -40 ~ 85°C

PVC : -30°C bis +85°C

:

www.lappkabel.de/en/cable-standradlengths

:

30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

가 VAT

가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® BUS IS

		/ mm ² /	(mm)	(kg/km)
PUR				
2170561	UNITRONIC® BUS IS PUR 2x6+2x2,5+1x4x0,5	2x6+2x2,5+1x4x0,5	15.6	182.4
PVC				
2170560	UNITRONIC® BUS IS PVC	2x6+2x2,5+1x4x0,5	15.6	182.4

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16